



FAG

★ NU1060-M1




Cylindrical roller bearing

Schaeffler ID:
0167374660000

★ Preferred product

Cylindrical roller bearing NU..-M1, with cage, single row, non-locating bearing, 2 ribs on outer ring, 0 ribs on inner ring (smooth), type NU

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	150 °C	Operating temperature max.
	43,14 kg	Weight

Main Dimensions & Performance Data

d	300 mm	Bore diameter
D	460 mm	Outside diameter
B	74 mm	Width
C_r	900.000 N	Basic dynamic load rating, radial
C_{0r}	1.430.000 N	Basic static load rating, radial
C_{ur}	122.000 N	Fatigue load limit, radial
n_G	2.290 1/min	Limiting speed
n_{gr}	1.390 1/min	Reference speed

Dimensions

r_{min}	4 mm	Minimum chamfer dimension
$r_{1 min}$	4 mm	Minimum chamfer dimension
s	7,9 mm	Axial displacement
E	420 mm	Raceway diameter outer ring
F	340 mm	Raceway diameter inner ring
$D_{1 min}$	405,2 mm	Minimum rib diameter outer ring

Mounting dimensions

$d_{a min}$	315 mm	Minimum diameter shaft shoulder
$d_{a max}$	336 mm	Maximum diameter of shaft shoulder
$d_{b min}$	345 mm	Minimum shaft shoulder
$D_{a max}$	445 mm	Maximum diameter of housing shoulder
$r_{a max}$	3 mm	Maximum recess radius
$r_{a1 max}$	3 mm	Maximum recess radius