



FAG

★ 22213-E1-XL

Spherical roller bearing

Schaeffler ID:
0167037660000Spherical roller bearings 222...-E1, main
dimensions to DIN 635-2

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	200 °C	Operating temperature max.
	1,476 kg	Weight

Main Dimensions & Performance Data

d	65 mm	Bore diameter
D	120 mm	Outside diameter
B	31 mm	Width
C_r	202.000 N	Basic dynamic load rating, radial
C_{0r}	210.000 N	Basic static load rating, radial
C_{ur}	26.500 N	Fatigue load limit, radial
n_G	7.000 1/min	Limiting speed
n_{gr}	4.200 1/min	Reference speed

Dimensions

r_{\min}	1,5 mm	Minimum chamfer dimension
D_1	107,3 mm	Bore diameter outer ring
d_2	79,1 mm	Raceway diameter of the inner ring
d_s	3,2 mm	Diameter lubrication hole
n_s	6,5 mm	Width of lubricating groove

Mounting dimensions

$d_{a\min}$	74 mm	Minimum diameter shaft shoulder
$D_{a\max}$	111 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1,5 mm	Maximum recess radius

Additional information

e	0,24	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2,81	Dynamic axial load factor
Y ₂	4,19	Dynamic axial load factor
Y ₀	2,75	Static axial load factor