

FAG

★ 22218-E1-XL-K

Spherical roller bearing


Schaeffler ID:
0167040880000

★ Preferred product

X-life

Spherical roller bearings 222...-E1-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
------------	--------	----------------------------

T_{\max}	200 °C	Operating temperature max.
------------	--------	----------------------------

	3,286 kg	Weight
--	----------	--------

Main Dimensions & Performance Data


d	90 mm	Bore diameter
D	160 mm	Outside diameter
B	40 mm	Width
C_r	345.000 N	Basic dynamic load rating, radial
C_{0r}	375.000 N	Basic static load rating, radial
C_{ur}	43.500 N	Fatigue load limit, radial
n_G	5.200 1/min	Limiting speed
n_{gr}	3.400 1/min	Reference speed

Dimensions

r_{\min}	2 mm	Minimum chamfer dimension
D_1	143,9 mm	Bore diameter outer ring
d_2	106,1 mm	Raceway diameter of the inner ring
d_s	3,2 mm	Diameter lubrication hole
n_s	6,5 mm	Width of lubricating groove

Mounting dimensions

$d_{a \min}$	101 mm	Minimum diameter shaft shoulder
$d_{a \max}$	106 mm	Maximum diameter of shaft shoulder
$D_{a \max}$	149 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2 mm	Maximum recess radius
$d_{b \min}$	96 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	10 mm	Minimum cavity width of the sleeve



Additional information

e	0,23	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
	H318	Adapter sleeve
Y ₁	2,9	Dynamic axial load factor
	AHX318	Withdrawal sleeve
Y ₂	4,31	Dynamic axial load factor
Y ₀	2,83	Static axial load factor