

FAG

★ NJ210-E-XL-TVP2

Cylindrical roller bearing


Schaeffler ID:
0167344160000

★ Preferred product

Cylindrical roller bearing NJ..-E-XL-TVP2,
with cage, single row, semi-locating
bearing, 2 ribs on outer ring, 1 rib on inner
ring, type NJ

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,484 kg	Weight

Main Dimensions & Performance Data

d	50 mm	Bore diameter
D	90 mm	Outside diameter
B	20 mm	Width
C_r	75.000 N	Basic dynamic load rating, radial
C_{0r}	69.000 N	Basic static load rating, radial
C_{ur}	11.300 N	Fatigue load limit, radial
n_G	9.700 1/min	Limiting speed
n_{gr}	6.600 1/min	Reference speed

Dimensions

r_{\min}	1,1 mm	Minimum chamfer dimension
$r_{1\min}$	1,1 mm	Minimum chamfer dimension
s	1,3 mm	Axial displacement
E	81,5 mm	Raceway diameter outer ring
F	59,5 mm	Raceway diameter inner ring
$D_{1\min}$	78,3 mm	Minimum rib diameter outer ring
d_1	64 mm	Maximum rib diameter inner ring

Mounting dimensions

$d_{a\min}$	57 mm	Minimum diameter shaft shoulder
$d_{a\max}$	58 mm	Maximum diameter of shaft shoulder
$D_{a\max}$	83 mm	Maximum diameter of housing shoulder
$d_{c\min}$	67 mm	Minimum shaft shoulder
$r_{a\max}$	1 mm	Maximum recess radius

Additional information

HJ210-E

L-washer

