



FAG


32308-B

Tapered roller bearing

Schaeffler ID:
0382788630000

Tapered roller bearings 323, main dimensions to DIN ISO 355 / DIN 720, separable, adjusted or in pairs

Technical information

**Main Dimensions & Performance Data**

d	40 mm	Bore diameter
D	90 mm	Outside diameter
B	33 mm	Width, inner ring
C	27 mm	Width, outer ring
T	35,25 mm	Width, total
C_r	120.000 N	Basic dynamic load rating, radial
C_{0r}	149.000 N	Basic static load rating, radial
C_{ur}	18.600 N	Fatigue load limit, radial
n_G	8.000 1/min	Limiting speed
n_{gr}	5.600 1/min	Thermal speed rating
	1,08 kg	Weight

Dimensions

$r_{1,2 \text{ min}}$	2 mm	Minimum chamfer dimension of inner ring back face
$r_{3,4 \text{ min}}$	1,5 mm	Minimum chamfer dimension of outer ring back face
a	28 mm	Distance between the apexes of the pressure cones
d_1	67 mm	Guidance rib diameter of inner ring

Mounting dimensions

$d_{a \text{ max}}$	50 mm	Maximum diameter of shaft shoulder
$d_{b \text{ min}}$	49 mm	Minimum diameter of shaft shoulder
$D_{a \text{ min}}$	69 mm	Minimum diameter of housing shoulder
$D_{a \text{ max}}$	81 mm	Maximum diameter of housing shoulder
$D_{b \text{ min}}$	85 mm	Minimum diameter of housing shoulder
$C_{a \text{ min}}$	4 mm	Minimum axial space
$C_{b \text{ min}}$	8 mm	Minimum axial space
$r_{a \text{ max}}$	2 mm	Maximum fillet radius of shaft
$r_{b \text{ max}}$	1,5 mm	Maximum fillet radius of housing

Calculation factors

e	0,55	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y	1,1	Dynamic axial load factor
Y ₀	0,6	Static axial load factor

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.