

FAG

## ★ NU228-E-XL-M1

Cylindrical roller bearing



Schaeffler ID:  
0167389340000

★ Preferred product

Cylindrical roller bearing NU...-E-XL-M1,  
with cage, single row, non-locating bearing,  
2 ribs on outer ring, 0 ribs on inner ring  
(smooth), type NU

X-life

## Technical information



## Temperature range

$T_{min}$	-30 °C	Operating temperature min.
$T_{max}$	150 °C	Operating temperature max.
	9,02 kg	Weight

## Main Dimensions &amp; Performance Data

d	140 mm	Bore diameter
D	250 mm	Outside diameter
B	42 mm	Width
$C_r$	460.000 N	Basic dynamic load rating, radial
$C_{0r}$	510.000 N	Basic static load rating, radial
$C_{ur}$	62.000 N	Fatigue load limit, radial
$n_G$	4.250 1/min	Limiting speed
$n_{gr}$	2.600 1/min	Reference speed

## Dimensions

$r_{min}$	3 mm	Minimum chamfer dimension
$r_{1 min}$	3 mm	Minimum chamfer dimension
s	3,8 mm	Axial displacement
E	225 mm	Raceway diameter outer ring
F	169 mm	Raceway diameter inner ring
$D_{1 min}$	216,7 mm	Minimum rib diameter outer ring

## Mounting dimensions

$d_{a min}$	154 mm	Minimum diameter shaft shoulder
$d_{a max}$	166 mm	Maximum diameter of shaft shoulder
$d_{b min}$	171 mm	Minimum shaft shoulder
$D_{a max}$	236 mm	Maximum diameter of housing shoulder
$r_{a max}$	2,5 mm	Maximum recess radius
$r_{a1 max}$	2,5 mm	Maximum recess radius

