



★ SL014936


Cylindrical roller bearing

Schaeffler ID:
0001220250000

★ Preferred product

Cylindrical roller bearings SL0149, locating bearing, double row, full complement cylindrical roller set, dimension series 49

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	10,312 kg	Weight

Main Dimensions & Performance Data

d	180 mm	Bore diameter
D	250 mm	Outside diameter
B	69 mm	Width
C_r	570.000 N	Basic dynamic load rating, radial
C_{0r}	1.200.000 N	Basic static load rating, radial
C_{ur}	149.000 N	Fatigue load limit, radial
n_G	1.480 1/min	Limiting speed
n_{gr}	920 1/min	Reference speed

Dimensions

r_{\min}	2 mm	Minimum chamfer dimension
d_1	204,9 mm	Maximum rib diameter inner ring
$D_{1\min}$	224,1 mm	Minimum rib diameter outer ring
$d_{c\min}$	204,5 mm	Minimum shaft shoulder
C	34,5 mm	Distance to lubrication hole

Mounting dimensions

$r_{a\max}$	2 mm	Maximum recess radius
$d_{a\min}$	204,9 mm	Minimum diameter shaft shoulder
$D_{a\max}$	224,5 mm	Maximum diameter of housing shoulder

Additional information

NNC4936V	Bearing designation DIN5412
----------	-----------------------------