


## Technical information



### Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.
	4,284 kg	Weight

### Main Dimensions & Performance Data

d	70 mm	Bore diameter
D	150 mm	Outside diameter
B	51 mm	Width
$C_r$	390.000 N	Basic dynamic load rating, radial
$C_{0r}$	390.000 N	Basic static load rating, radial
$C_{ur}$	37.500 N	Fatigue load limit, radial
$n_G$	4.800 1/min	Limiting speed
$n_{gr}$	3.700 1/min	Reference speed

### Dimensions

$r_{\min}$	2,1 mm	Minimum chamfer dimension
$D_1$	128 mm	Bore diameter outer ring
$d_2$	86,7 mm	Raceway diameter of the inner ring
$d_s$	4,8 mm	Diameter lubrication hole
$n_s$	9,5 mm	Width of lubricating groove

### Mounting dimensions

$d_{a \min}$	82 mm	Minimum diameter shaft shoulder
$D_{a \max}$	138 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2,1 mm	Maximum recess radius

**Additional information**

e	0,34	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y <sub>1</sub>	2	Dynamic axial load factor
Y <sub>2</sub>	2,98	Dynamic axial load factor
Y <sub>0</sub>	1,96	Static axial load factor