

FAG

★ NU1018-XL-M1

Cylindrical roller bearing



Schaeffler ID:
0190046720000

★ Preferred product

Cylindrical roller bearing NU...-XL-M1, with cage, single row, non-locating bearing, 2 ribs on outer ring, 0 ribs on inner ring (smooth), type NU

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	150 °C	Operating temperature max.
	1,32 kg	Weight

Main Dimensions & Performance Data

d	90 mm	Bore diameter
D	140 mm	Outside diameter
B	24 mm	Width
C_r	111.000 N	Basic dynamic load rating, radial
C_{0r}	124.000 N	Basic static load rating, radial
C_{ur}	16.600 N	Fatigue load limit, radial
n_G	8.400 1/min	Limiting speed
n_{gr}	4.550 1/min	Reference speed

Dimensions

r_{\min}	1,5 mm	Minimum chamfer dimension
$r_{1\min}$	1,1 mm	Minimum chamfer dimension
s	3 mm	Axial displacement
E	127 mm	Raceway diameter outer ring
F	103 mm	Raceway diameter inner ring
$D_{1\min}$	122,9 mm	Minimum rib diameter outer ring

Mounting dimensions

$d_{a\min}$	96 mm	Minimum diameter shaft shoulder
$d_{a\max}$	101 mm	Maximum diameter of shaft shoulder
$d_{b\min}$	106 mm	Minimum shaft shoulder
$D_{a\max}$	133 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1,5 mm	Maximum recess radius
$r_{a1\max}$	1 mm	Maximum recess radius

