

FAG



★ 1201-TVH

Self-aligning ball bearing

Schaeffler ID:
0167002360000Self-aligning ball bearing 12..-TVH, plastic
cage

★ Preferred product

Technical information



Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.
	0,04 kg	Weight

Main Dimensions & Performance Data

d	12 mm	Bore diameter
D	32 mm	Outside diameter
B	10 mm	Width
r _{min}	0,6 mm	Minimum chamfer dimension
C _r	5.700 N	Basic dynamic load rating, radial
C _{0r}	1.270 N	Basic static load rating, radial
C _{ur}	80 N	Fatigue load limit, radial
n _G	28.000 1/min	Limiting speed
n _{gr}	21.300 1/min	Reference speed

Dimensions

D ₁	25,1 mm	Shoulder diameter outer ring
d ₁	18,2 mm	Shoulder diameter inner ring

Mounting dimensions

d _{a min}	16,2 mm	Minimum diameter shaft shoulder
D _{a max}	27,8 mm	Maximum diameter of housing shoulder
r _{a max}	0,6 mm	Maximum fillet radius

Calculation factors

e	0,37	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	1,68	Dynamic axial load factor
Y ₂	2,61	Dynamic axial load factor
Y ₀	1,76	Static axial load factor