



FAG



★ 1216-K-TVH-C3

Self-aligning ball bearing

Schaeffler ID:
0389033000030Self-aligning ball bearing 12..-K-TVH,
tapered bore taper 1:12, plastic cage

★ Preferred product

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	1,62 kg	Weight

Main Dimensions & Performance Data

d	80 mm	Bore diameter
D	140 mm	Outside diameter
B	26 mm	Width
r_{\min}	2 mm	Minimum chamfer dimension
C_r	40.000 N	Basic dynamic load rating, radial
C_{0r}	17.000 N	Basic static load rating, radial
C_{ur}	1.020 N	Fatigue load limit, radial
n_G	5.300 1/min	Limiting speed
n_{gr}	5.100 1/min	Reference speed

Dimensions

D_1	122,1 mm	Shoulder diameter outer ring
d_1	101,8 mm	Shoulder diameter inner ring

Mounting dimensions

$d_{a \min}$	91 mm	Minimum diameter shaft shoulder
$d_{a \max}$	99 mm	Maximum diameter shaft shoulder
$D_{a \max}$	129 mm	Maximum diameter of housing shoulder
$d_{b \min}$	85 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	5 mm	Minimum cavity width of the sleeve
$r_{a \max}$	2 mm	Maximum fillet radius

Calculation factors

e	0,16	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
	H216	Adapter sleeve
Y ₁	3,93	Dynamic axial load factor
Y ₂	6,08	Dynamic axial load factor
Y ₀	4,12	Static axial load factor