



FAG

★ 61821-2RSR-Y

Deep groove ball bearing

Schaeffler ID:
0807289440000Deep groove ball bearing 618...-2RSR-Y,
single row, seals, brass sheet metal cage

★ Preferred product

Technical information



Temperature range

| | | |
|------------|----------|----------------------------|
| T_{\min} | -20 °C | Operating temperature min. |
| T_{\max} | 110 °C | Operating temperature max. |
| | 0,004 kg | Weight |

Main Dimensions & Performance Data

| | | |
|----------|-------------|-----------------------------------|
| d | 105 mm | Bore diameter |
| D | 130 mm | Outside diameter |
| B | 13 mm | Width |
| C_r | 22.100 N | Basic dynamic load rating, radial |
| C_{0r} | 23.600 N | Basic static load rating, radial |
| C_{ur} | 1.320 N | Fatigue load limit, radial |
| n_G | 2.360 1/min | Limiting speed |

Dimensions

| | | |
|------------|----------|------------------------------|
| r_{\min} | 1 mm | Minimum chamfer dimension |
| D_2 | 124,2 mm | Caliber diameter outer ring |
| d_1 | 113,2 mm | Shoulder diameter inner ring |

Mounting dimensions

| | | |
|-------------|----------|--------------------------------------|
| $d_{a\min}$ | 109,6 mm | Minimum diameter shaft shoulder |
| $D_{a\max}$ | 125,4 mm | Maximum diameter of housing shoulder |
| $r_{a\max}$ | 1 mm | Maximum fillet radius |

Calculation factors

| | | |
|-------|------|--------------------|
| f_0 | 15,9 | Calculation factor |
|-------|------|--------------------|