




SL182992-TB

Cylindrical roller bearing

Schaeffler ID:
0572464160000

Cylindrical roller bearing SL1829..-TB, full complement roller set, single row, semi-locating bearing, 1 rib on outer ring, 2 ribs on inner ring, type SL18

Technical information



Main Dimensions & Performance Data

d	460 mm	Bore diameter
D	620 mm	Outside diameter
B	95 mm	Width
C_r	2.130.000 N	Basic dynamic load rating, radial
C_{0r}	4.250.000 N	Basic static load rating, radial
C_{ur}	430.000 N	Fatigue load limit, radial
n_G	570 1/min	Limiting speed
n_{gr}	310 1/min	Reference speed
	79,55 kg	Weight

Dimensions

r_{min}	4 mm	Minimum chamfer dimension
s	7 mm	Axial displacement
d_1	504 mm	Maximum rib diameter inner ring
D_{1min}	559,6 mm	Minimum rib diameter outer ring
E	576,3 mm	Raceway diameter outer ring

Mounting dimensions

d_{amin}	504 mm	Minimum diameter shaft shoulder
d_{cmin}	504 mm	Minimum shaft shoulder
D_{amax}	559,5 mm	Maximum diameter of housing shoulder
D_{emin}	576 mm	Minimum diameter of housing shoulder
r_{amax}	4 mm	Maximum recess radius

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.