

SAKG 28 I**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image

Are you looking for an interface from electrical engineering to electronics? To be able to feed through to the electronic devices on the panel sometimes a solder connection or a standard pluggable solution is appropriate.

General ordering data

Version	SAK Series, Feed-through terminal, Rated cross-section: 35 mm ² , Screw connection
Order No.	0170020000
Type	SAKG 28 I
GTIN (EAN)	4008190152000
Qty.	10 pc(s).

SAKG 28 I

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Depth	63.5 mm	Depth (inches)	2.5 inch
Height	70 mm	Height (inches)	2.756 inch
Width	28 mm	Width (inches)	1.102 inch
Net weight	100.5 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Material data

Material	KrG	Colour	beige
UL 94 flammability rating	V-0, 5VA		

System specifications

Version	Stud terminal / ZB	End cover plate required	Yes
Number of potentials	1	Number of levels	1
Number of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 32	N-function	No
PE function	No	PEN function	No

Additional technical data

Explosion-tested version	No	Number of similar terminals	1
Open sides	Open	Type of mounting	Snap-on

CSA rating data

Certificate No. (CSA)	12400-244	Current size C (CSA)	110 A
Voltage size C (CSA)	600 V	Wire cross section max. (CSA)	1 AWG
Wire cross section min. (CSA)	6 AWG		

Conductors for clamping (rated connection)

Clamping range, max.	50 mm ²	Clamping range, min.	6 mm ²
Clamping screw	M 6	Connection cross-section, stranded, max.	50 mm ²
Connection cross-section, stranded, min.	6 mm ²	Connection direction	on side
Gauge to IEC 60947-1	B9	Number of connections	1
Stripping length	15 mm	Tightening torque, max.	6 Nm
Tightening torque, min.	4 Nm	Type of connection	Screw connection
Wire connection cross section AWG, max.	AWG 1	Wire connection cross section AWG, min.	AWG 6
Wire connection cross section, finely stranded, max.	35 mm ²	Wire connection cross section, finely stranded, min.	10 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	35 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	6 mm ²
Wire connection cross-section, solid core, max.	16 mm ²	Wire connection cross-section, solid core, min.	6 mm ²

Creation date March 6, 2023 8:54:23 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

2

SAKG 28 I

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

Technical data

General

Rail	TS 32	Standards	www.weidmueller.com IEC 60947-7-1
Wire connection cross section AWG, max.	AWG 1	Wire connection cross section AWG, min.	AWG 6

Rating data

Rated cross-section	35 mm ²	Rated voltage	1,000 V
Rated current	125 A	Current at maximum wires	150 A
Standards	IEC 60947-7-1	Volume resistance according to IEC 60947-7-x	0.26 mΩ
Rated impulse withstand voltage	8 kV	Power loss in accordance with IEC 60947-7-x	4 W
Pollution severity	3		

UL rating data

Certificate No. (UR)	E60693	Conductor size Factory wiring max. (UR)	2 AWG
Conductor size Factory wiring min. (UR)	8 AWG	Conductor size Field wiring max. (UR)	2 AWG
Conductor size Field wiring min. (UR)	8 AWG	Current size C (UR)	95 A
Voltage size C (UR)	600 V		

Classifications

ETIM 6.0	EC000897	ETIM 7.0	EC000897
ETIM 8.0	EC000897	ECLASS 9.0	27-14-11-20
ECLASS 9.1	27-14-11-20	ECLASS 10.0	27-14-11-20
ECLASS 11.0	27-14-11-20	ECLASS 12.0	27-14-11-20

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	999cd67e-471e-4085-8dba-1342fcea86de

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E60693
Certificate No. (cURusEX)	E184763

Downloads

Approval/Certificate/Document of Conformity	EAC certificate MARITREG Certificate Declaration of Conformity CE Declaration of Conformity all terminals UKCA declaration of conformity
Engineering Data	WSCAD
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format

Creation date March 6, 2023 8:54:23 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.