



GE160-DO

Spherical plain bearing

Schaeffler ID:
0066483200000

Radial spherical plain bearing, requiring maintenance, sliding contact surface: steel/steel, DIN ISO 12240-1, dimension series E, open design

Technical information

Main Dimensions & Performance Data

d	160 mm	Bore diameter bearing
D	230 mm	Outside diameter bearing
B	105 mm	Width Inner ring
C_r	1.360.000 N	Basic dynamic load rating, radial
C_{0r}	6.800.000 N	Basic static load rating, radial
	13,8 kg	Weight

Dimensions

C	80 mm	Width Outer ring
d_K	200 mm	Ball diameter
α	8 °	Tilt angle
$r_{1\text{min}}$	1 mm	Edge Spacing
$r_{2\text{min}}$	1 mm	Edge Spacing
d_{OT}	0 mm	Bore diameter bearing, upper tolerance
d_{UT}	-0,025 mm	Bore diameter bearing, lower tolerance
D_{OT}	0 mm	Outside diameter, upper tolerance
D_{UT}	-0,03 mm	Outside diameter, lower tolerance
B_{OT}	0 mm	Width inner ring, upper tolerance
G_r	0,1 - 0,192 mm	Radial Clearance
B_{UT}	-0,25 mm	Width inner ring, lower tolerance
C_{OT}	0 mm	Width outer ring, upper tolerance
C_{UT}	-0,6 mm	Width outer ring, lower tolerance

Mounting dimensions

$d_{a\text{max}}$	170,2 mm	Connection measure Inner ring
$D_{a\text{min}}$	191 mm	Housing Connection Diameter

Temperature range

T_{min}	-60 °C	Operating temperature min.
T_{max}	200 °C	Operating temperature max.

