



FAG

**23964-MB**

Spherical roller bearing

Schaeffler ID:  
0167090550000Spherical roller bearing 239..-MB,  
symmetric 3 ribs

## Technical information

**Main Dimensions & Performance Data**

|          |             |                                   |
|----------|-------------|-----------------------------------|
| d        | 320 mm      | Bore diameter                     |
| D        | 440 mm      | Outside diameter                  |
| B        | 90 mm       | Width                             |
| $C_r$    | 1.310.000 N | Basic dynamic load rating, radial |
| $C_{0r}$ | 2.750.000 N | Basic static load rating, radial  |
| $C_{ur}$ | 206.000 N   | Fatigue load limit, radial        |
| $n_G$    | 1.700 1/min | Limiting speed                    |
| $n_{gr}$ | 930 1/min   | Reference speed                   |
|          | 40,8 kg     | Weight                            |

**Additional information**

|           |          |                             |
|-----------|----------|-----------------------------|
| $r_{min}$ | 3 mm     | Minimum chamfer dimension   |
| $D_1$     | 406,2 mm | Bore diameter outer ring    |
| $d_s$     | 9,5 mm   | Diameter lubrication hole   |
| $n_s$     | 17,7 mm  | Width of lubricating groove |

**Mounting dimensions**

|             |          |                                      |
|-------------|----------|--------------------------------------|
| $d_{a min}$ | 332,4 mm | Minimum diameter shaft shoulder      |
| $D_{a max}$ | 427,6 mm | Maximum diameter of housing shoulder |
| $r_{a max}$ | 2,5 mm   | Maximum recess radius                |

**Calculation factors**

|       |      |  |
|-------|------|--|
| e     | 0,19 | Limiting value of $F_a/F_r$ for the applicability of diff. Values of factors X and Y |
| $Y_1$ | 3,62 | Dynamic axial load factor  |
| $Y_2$ | 5,39 | Dynamic axial load factor  |
| $Y_0$ | 3,54 | Static axial load factor   |

**Temperature range**

|           |        |                            |
|-----------|--------|----------------------------|
| $T_{min}$ | -30 °C | Operating temperature min. |
| $T_{max}$ | 200 °C | Operating temperature max. |