

★ SL014848



Cylindrical roller bearing

Schaeffler ID:
0001650420000

★ Preferred product

Cylindrical roller bearings, locating bearing, double row, full complement cylindrical roller set, dimension series 48

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	10 kg	Weight

Main Dimensions & Performance Data

d	240 mm	Bore diameter
D	300 mm	Outside diameter
B	60 mm	Width
C_r	510.000 N	Basic dynamic load rating, radial
C_{0r}	1.260.000 N	Basic static load rating, radial
C_{ur}	145.000 N	Fatigue load limit, radial
n_G	1.170 1/min	Limiting speed
n_{gr}	730 1/min	Reference speed

Dimensions

r_{\min}	2 mm	Minimum chamfer dimension
d_1	259,5 mm	Maximum rib diameter inner ring
$D_{1\min}$	276,7 mm	Minimum rib diameter outer ring
$d_{c\min}$	259,5 mm	Minimum shaft shoulder
C	30 mm	Distance to lubrication hole

Mounting dimensions

$r_{a\max}$	2 mm	Maximum recess radius
$d_{a\min}$	259,5 mm	Minimum diameter shaft shoulder
$D_{a\max}$	277 mm	Maximum diameter of housing shoulder

Additional information

NNC4848V	Bearing designation DIN5412
----------	-----------------------------