

★ SL182913-XL

Cylindrical roller bearing




Schaeffler ID:
0502196850000

★ Preferred product

Cylindrical roller bearing SL18, full complement roller set, single row, semi-locating bearing, 1 rib on outer ring, 2 ribs on inner ring, type SL18

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,003 kg	Weight

Main Dimensions & Performance Data

d	65 mm	Bore diameter
D	90 mm	Outside diameter
B	16 mm	Width
C_r	67.000 N	Basic dynamic load rating, radial
C_{0r}	84.000 N	Basic static load rating, radial
C_{ur}	15.400 N	Fatigue load limit, radial
n_G	4.250 1/min	Limiting speed
n_{gr}	2.550 1/min	Reference speed

Dimensions

r_{\min}	1 mm	Minimum chamfer dimension
s	1 mm	Axial displacement
d_1	75,7 mm	Maximum rib diameter inner ring
$D_{1\min}$	81 mm	Minimum rib diameter outer ring
E	85,2 mm	Raceway diameter outer ring

Mounting dimensions

$d_{a\min}$	75,7 mm	Minimum diameter shaft shoulder
$d_{c\min}$	75,5 mm	Minimum shaft shoulder
$D_{a\max}$	81 mm	Maximum diameter of housing shoulder
$D_{e\min}$	85 mm	Minimum diameter of housing shoulder
$r_{a\max}$	1 mm	Maximum recess radius