

## CLI C 02-3 GE/SW H MP

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

Version	CableLine, Conductor and cable markers, 1.3 - 3 mm, 3 x 3.4 mm, yellow
Order No.	<a href="#">0252111651</a>
Type	CLI C 02-3 GE/SW H MP
GTIN (EAN)	4008190178840
Qty.	200 pc(s).

## CLI C 02-3 GE/SW H MP

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	3.5 mm	Depth (inches)	0.138 inch
Height	3 mm	Height (inches)	0.118 inch
Width	3.4 mm	Width (inches)	0.134 inch
Net weight	0.03 g		

## Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

## General data

Colour	yellow	Colour of printing	black
Halogen	Yes	Material	PVC, soft, without Cadmium
Material colour according to resistance code	4	Number of markers per combination	1 Component part = Conductor and cable markers
Operating temperature range	-30...80 °C	Operating temperature range, max.	80 °C
Operating temperature range, min.	-30 °C	Orientation of print	horizontal
Printed characters	Upper-case letters	Printing	H
Printing method	hot-embossing	Recommended industries	Process, Machinery
Type of printing	Standard	UL 94 flammability rating	V-0
Version	MultiPack	Width	3.4 mm

## Conductor and cable markers

Conductor O.D.	1.3 - 3 mm	Conductor O.D., max.	3 mm
Conductor O.D., min.	1.3 mm	Conductor cross-section, max.	1.5 mm <sup>2</sup>
Conductor cross-section, min.	0.2 mm <sup>2</sup>	Cross-section for connected wire	0.2 - 1.5 mm <sup>2</sup>
Halogen	Yes		

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">WSCAD</a>
Product Change Notification	<a href="#">PCN CableLine_DE</a> <a href="#">PCN CableLine_EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**CLI C 02-3 GE/SW H MP**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



Similar to illustration