

## CLI C 3-6 GE/SW 3 MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

|            |                                                                      |
|------------|----------------------------------------------------------------------|
| Version    | CableLine, Conductor and cable markers, 8 - 16 mm, 6 x 11 mm, yellow |
| Order No.  | <a href="#">0253411511</a>                                           |
| Type       | CLI C 3-6 GE/SW 3 MP                                                 |
| GTIN (EAN) | 4008 190085377                                                       |
| Qty.       | 20 pc(s).                                                            |

Creation date May 4, 2023 4:00:23 PM CEST

Catalogue status 28.04.2023 / We reserve the right to make technical changes.

## CLI C 3-6 GE/SW 3 MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 17 mm  | Depth (inches)  | 0.669 inch |
| Height     | 6 mm   | Height (inches) | 0.236 inch |
| Width      | 11 mm  | Width (inches)  | 0.433 inch |
| Net weight | 0.72 g |                 |            |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

### General data

|                                   |                                                |                                              |               |
|-----------------------------------|------------------------------------------------|----------------------------------------------|---------------|
| Colour                            | yellow                                         | Colour of printing                           | black         |
| Halogen                           | Yes                                            | Insulation cross-section, max.               | 16            |
| Material                          | PVC, soft, without Cadmium                     | Material colour according to resistance code | 4             |
| Number of markers per combination | 1 Component part = Conductor and cable markers | Operating temperature range                  | -30...80 °C   |
| Operating temperature range, max. | 80 °C                                          | Operating temperature range, min.            | -30 °C        |
| Orientation of print              | horizontal                                     | Printed characters                           | Numbers       |
| Printing                          | 3                                              | Printing method                              | hot-embossing |
| Type of printing                  | Standard                                       | UL 94 flammability rating                    | V-0           |
| Version                           | MultiPack                                      | Width                                        | 11 mm         |

### Conductor and cable markers

|                               |                    |                                  |                         |
|-------------------------------|--------------------|----------------------------------|-------------------------|
| Conductor O.D.                | 8 - 16 mm          | Conductor O.D., max.             | 16 mm                   |
| Conductor O.D., min.          | 8 mm               | Conductor cross-section, max.    | 70 mm <sup>2</sup>      |
| Conductor cross-section, min. | 16 mm <sup>2</sup> | Cross-section for connected wire | 16 - 70 mm <sup>2</sup> |
| Halogen                       | Yes                |                                  |                         |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                             |                                                                      |
|-----------------------------|----------------------------------------------------------------------|
| Engineering Data            | <a href="#">WSCAD</a>                                                |
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |

**Data sheet**

**CLI C 3-6 GE/SW 3 MP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



Similar to illustration