

CLI C 3-6 GE/SW D MP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

| | |
|------------|--|
| Version | CableLine, Conductor and cable markers, 8 - 16 mm, 6 x 11 mm, yellow |
| Order No. | 0253411643 |
| Type | CLI C 3-6 GE/SW D MP |
| GTIN (EAN) | 4008190118785 |
| Qty. | 20 pc(s). |

Creation date May 2, 2023 2:54:50 PM CEST

Catalogue status 28.04.2023 / We reserve the right to make technical changes.

CLI C 3-6 GE/SW D MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 17 mm | Depth (inches) | 0.669 inch |
| Height | 6 mm | Height (inches) | 0.236 inch |
| Width | 11 mm | Width (inches) | 0.433 inch |
| Net weight | 0.75 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

General data

| | | | |
|-----------------------------------|--|--|--------------------|
| Colour | yellow | Colour of printing | black |
| Halogen | Yes | Insulation cross-section, max. | 16 |
| Material | PVC, soft, without Cadmium | Material colour according to resistance code | 4 |
| Number of markers per combination | 1 Component part = Conductor and cable markers | Operating temperature range | -30...80 °C |
| Operating temperature range, max. | 80 °C | Operating temperature range, min. | -30 °C |
| Orientation of print | horizontal | Printed characters | Upper-case letters |
| Printing | D | Printing method | hot-embossing |
| Type of printing | Standard | UL 94 flammability rating | V-0 |
| Version | MultiPack | Width | 11 mm |

Conductor and cable markers

| | | | |
|-------------------------------|--------------------|----------------------------------|-------------------------|
| Conductor O.D. | 8 - 16 mm | Conductor O.D., max. | 16 mm |
| Conductor O.D., min. | 8 mm | Conductor cross-section, max. | 70 mm ² |
| Conductor cross-section, min. | 16 mm ² | Cross-section for connected wire | 16 - 70 mm ² |
| Halogen | Yes | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|-----------------------------|--|
| Engineering Data | WSCAD |
| Product Change Notification | PCN CableLine_DE PCN CableLine_EN |
| Catalogues | Catalogues in PDF-format |

Data sheet

CLI C 3-6 GE/SW D MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Similar to illustration