

CLI C 3-6 GE/SW O MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Version	CableLine, Conductor and cable markers, 8 - 16 mm, 6 x 11 mm, yellow
Order No.	0253411665
Type	CLI C 3-6 GE/SW O MP
GTIN (EAN)	4008 190082178
Qty.	20 pc(s).

Creation date May 4, 2023 4:04:14 PM CEST

Catalogue status 28.04.2023 / We reserve the right to make technical changes.

CLI C 3-6 GE/SW O MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	17 mm	Depth (inches)	0.669 inch
Height	6 mm	Height (inches)	0.236 inch
Width	11 mm	Width (inches)	0.433 inch
Net weight	0.75 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

General data

Colour	yellow	Colour of printing	black
Halogen	Yes	Insulation cross-section, max.	16
Material	PVC, soft, without Cadmium	Material colour according to resistance code	4
Number of markers per combination	1 Component part = Conductor and cable markers	Operating temperature range	-30...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Orientation of print	horizontal	Printed characters	Upper-case letters
Printing	O	Printing method	hot-embossing
Type of printing	Standard	UL 94 flammability rating	V-0
Version	MultiPack	Width	11 mm

Conductor and cable markers

Conductor O.D.	8 - 16 mm	Conductor O.D., max.	16 mm
Conductor O.D., min.	8 mm	Conductor cross-section, max.	70 mm ²
Conductor cross-section, min.	16 mm ²	Cross-section for connected wire	16 - 70 mm ²
Halogen	Yes		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD
Product Change Notification	PCN CableLine_DE PCN CableLine_EN
Catalogues	Catalogues in PDF-format

Data sheet

CLI C 3-6 GE/SW O MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Similar to illustration