

## CLI C 3-6 GE/SW V MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

|            |  |
|------------|--|
| Version    | CableLine, Conductor and cable markers, 8 - 16 mm, 6 x 11 mm, yellow |
| Order No.  | <a href="#">0253411681</a>   |
| Type       | CLI C 3-6 GE/SW V MP   |
| GTIN (EAN) | 4008190128708  |
| Qty.       | 20 pc(s).  |

Creation date May 4, 2023 4:05:14 PM CEST

Catalogue status 28.04.2023 / We reserve the right to make technical changes.

## CLI C 3-6 GE/SW V MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Depth      | 17 mm | Depth (inches)  | 0.669 inch |
| Height     | 6 mm  | Height (inches) | 0.236 inch |
| Width      | 11 mm | Width (inches)  | 0.433 inch |
| Net weight | 0.7 g |                 |            |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

### General data

|                                   |  |  |                    |
|-----------------------------------|--|--|--------------------|
| Colour                            | yellow   | Colour of printing                           | black              |
| Halogen                           | Yes  | Insulation cross-section, max.               | 16                 |
| Material                          | PVC, soft, without Cadmium                     | Material colour according to resistance code | 4                  |
| Number of markers per combination | 1 Component part = Conductor and cable markers | Operating temperature range                  | -30...80 °C        |
| Operating temperature range, max. | 80 °C  | Operating temperature range, min.            | -30 °C             |
| Orientation of print              | horizontal                                     | Printed characters                           | Upper-case letters |
| Printing                          | V  | Printing method                              | hot-embossing      |
| Type of printing                  | Standard                                       | UL 94 flammability rating                    | V-0                |
| Version                           | MultiPack                                      | Width  | 11 mm              |

### Conductor and cable markers

|                               |                    |                                  |                         |
|-------------------------------|--------------------|----------------------------------|-------------------------|
| Conductor O.D.                | 8 - 16 mm          | Conductor O.D., max.             | 16 mm                   |
| Conductor O.D., min.          | 8 mm               | Conductor cross-section, max.    | 70 mm <sup>2</sup>      |
| Conductor cross-section, min. | 16 mm <sup>2</sup> | Cross-section for connected wire | 16 - 70 mm <sup>2</sup> |
| Halogen                       | Yes                |                                  |                         |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">WSCAD</a>  |
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |

**Data sheet**

**CLI C 3-6 GE/SW V MP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



Similar to illustration