

ZB 16 ZKSC**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image

Uninsulated bus bar tap-off terminals offer a space-saving option for connecting conductors on a bus bar.

General ordering data

Version	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping yoke, Feed-through (bushing)
Order No.	031660000
Type	ZB 16 ZKSC
GTIN (EAN)	4008190145989
Qty.	50 pc(s).

ZB 16 ZKSC
Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com
www.weidmueller.com
Technical data
Dimensions and weights

Depth	24 mm	Depth (inches)	0.945 inch
Height	16 mm	Height (inches)	0.63 inch
Width	10 mm	Width (inches)	0.394 inch
Net weight	7.52 g		

Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

Rating data IECEx/ATEX

Certificate No. (IECEX)	IECEXULD13.0005U	Wire cross section max. (IECEX)	16 mm ²
-------------------------	------------------	---------------------------------	--------------------

Safety notice

Installation instructions:
 The potential equalisation (PE) rail modules are suitable for use in housings in atmospheres with flammable gases and dust. For use in areas with flammable gases, these housings must meet the requirements of EN 60079-0 and EN 60079-7. For use in areas with flammable dust, these housings must meet the requirements of EN 60079-0 and EN 60079-31.

When combined with other terminal block ranges and sizes, and when other accessories are used, you must comply with the clearance and creepage distances given. Regarding accessory use, the manufacturer's instructions must be followed.

List of restrictions:
 The PE rail modules are considered one component, with Ex marking when used with the busbar holders of type SH and WEW. When used independently, the above named components are not covered by this certificate.

System specifications

Version	for busbar 10 x 3 mm
---------	----------------------

Additional technical data

Installation advice	Feed-through (bushing)	Type of mounting	when screwed in
---------------------	------------------------	------------------	-----------------

ZB 16 ZKSC

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

CSA rating data

Certificate No. (CSA)	12400-237	Wire cross section max. (CSA)	6 AWG
Wire cross section min. (CSA)	12 AWG		

Conductors for clamping (rated connection)

Clamping range, max.	25 mm ²	Clamping range, min.	2.5 mm ²
Clamping screw	M 4	Connection cross-section, stranded, max.	25 mm ²
Connection cross-section, stranded, min.	16 mm ²	Stripping length	16 mm
Tightening torque, min.	2.6 Nm	Type of connection	Clamping yoke
Wire connection cross section, finely stranded, max.	16 mm ²	Wire connection cross section, finely stranded, min.	2.5 mm ²
Wire connection cross-section, solid core, max.	16 mm ²	Wire connection cross-section, solid core, min.	2.5 mm ²

Dimensions

TS 35 offset	39 mm
--------------	-------

General


Installation advice	Feed-through (bushing)
---------------------	------------------------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-46	ECLASS 12.0	27-14-11-46

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURusEX)	E184763

Downloads

Approval/Certificate/Document of Conformity	Attestation of Conformity ATEX Certificate IECEX Certificate UKCA Certificate
Engineering Data	CAD data – 41549_ZB_16_ZKSC_DXF.dxf CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
User Documentation	Installation Instruction Storage Conditions Terminal Blocks NTI ZB WBB
Catalogues	Catalogues in PDF-format
Brochures	

Creation date March 3, 2023 1:00:10 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.