

Q 3 SAK4**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 3
Order No.	0336800000
Type	Q 3 SAK4
GTIN (EAN)	4008190089795
Qty.	50 pc(s).

Q 3 SAK4

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Depth	20.5 mm	Depth (inches)	0.807 inch
Height	6 mm	Height (inches)	0.236 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	7.36 g		

Temperatures

Storage temperature -25 °C...55 °C

Material data

Material CuSn Colour grey

System specifications

Version for cross-connection link

Additional technical data

Explosion-tested version No Installation advice Direct mounting
Type of fixing when screwed in

Cross-connector

Number of cross-connected terminals 3 Rated current, 2-pole 41 A
Rated current, multi-pole 41 A Type Cross-connector

Dimensions

Pitch in mm (P) 6 mm

General

Installation advice Direct mounting Number of poles 3

Rating data

Rated current 32 A

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

Approvals

Approvals



ROHS Conform

Creation date March 6, 2023 9:33:40 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

Q 3 SAK4**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.comwww.weidmueller.com**Technical data****Downloads**Approval/Certificate/Document of
Conformity[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)