

**TBF 30/30/18 7035**
**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Similar to illustration**


The enclosures of the TBF series are made of extremely tough glass fibre-reinforced polyester. These enclosures are ideal for applications that call for low weight coupled with high shock resistance. The weather-resistant TBF enclosures are designed for a wide range of applications. Together with their comprehensive range of accessories, they provide universal solutions for accommodating built-in items such as regulators, measuring instruments, valves and other equipment.

**Features:**

- 9 sizes in 2 versions, with grey and transparent lids
- Cover with nylon screws
- Fixing holes outside the sealed area
- Thread for fitting to terminal rails and mounting plates
- Comprehensive accessories
- Weidmüller can manufacture and supply this enclosure to match customer specifications, fitted with all necessary terminals and cable glands.

**General ordering data**

Version	TBF (polyester empty enclosure), Empty enclosure, Height: 302 mm, Width: 302 mm, Depth: 175 mm, Material: Glass fibre-reinforced polyester, lacquered, Light Grey
Order No.	<a href="#">0360300000</a>
Type	TBF 30/30/18 7035
GTIN (EAN)	4032248002153
Qty.	1 pc(s).

## TBF 30/30/18 7035

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	175 mm	Depth (inches)	6.89 inch
Height	302 mm	Height (inches)	11.89 inch
Width	302 mm	Width (inches)	11.89 inch
Net weight	2,420 g		

## Temperatures

Operating temperature	-50 °C...130 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	130 °C		

## Cable glands, right

M12	44	M16	24
M20	20	M25	10
M32	4	M40	3
M50	3	M63	2

## Cable glands, top/bottom

M12	44	M16	24
M20	20	M25	10
M32	4	M40	3
M50	3	M63	2

## Certificate numbers enclosure

Certificate No. (EAC)	RUC-DE.BE02.B.00173	Certificate no. Terminal Box (EAC)	RU C-DE.BE02.B.00173 Ind. Terminal Box
-----------------------	---------------------	------------------------------------	---

## General information

Access opening: height	276 mm	Access opening: width	276 mm
Areas of use	Building systems and technology, Transportation, Packaging industry, Machine construction	Enclosure attachment	6.5 mm hole in enclosure base
Flange plate	No	Impact resistance	IK08 in accordance with IEC 62208, IK10 in accordance with IEC 62262
Integral fixing	4 or 6 stud bolts M6 inner (female) thread	Lid	Yes
Lid attachment	Crosshead nylon screws	Material	Glass fibre-reinforced polyester
Number of lid screws	4	Operating temperature, max.	130 °C
Operating temperature, min.	-50 °C	Protection degree	IP67
Seal material	Polyurethane	Standards	IEC 60529, EN 60529, EN 62208, EN/IEC 61439-2
Surface finish	lacquered	Torque for lid screws	1.5 Nm
Toxicity	Free from halogens	UL 94 flammability rating	HB

## horizontal assembly

WDU 10 / ZDU 10	1x22	WDU 16 / ZDU 16	1x16
WDU 2,5 / ZDU 2,5 / IDU 2,5	1x44	WDU 35 / ZDU 35	1x14
WDU 4 / ZDU 4	1x37	WDU 6 / ZDU 6	1x28

Creation date February 28, 2023 12:47:43 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

TBF 30/30/18 7035

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

## Technical data

info@weidmueller.com

www.weidmueller.com

2x16

2x14

2x28

## vertical assembly

WDU 10 / ZDU 10	2x22	WDU 16 / ZDU 16	2x16
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x44	WDU 35 / ZDU 35	2x14
WDU 4 / ZDU 4	2x37	WDU 6 / ZDU 6	2x28

## Classifications

ETIM 6.0	EC000261	ETIM 7.0	EC000261
ETIM 8.0	EC000261	ECLASS 9.0	27-18-01-01
ECLASS 9.1	27-18-92-90	ECLASS 10.0	27-18-01-01
ECLASS 11.0	27-18-01-01	ECLASS 12.0	27-18-01-01

## Approvals

Approvals



ROHS

Conform

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">RU C-DE.BE02.B.00173 - Ind. Terminal Box</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**TBF 30/30/18 7035**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Drawings**

