

**DKT 4/35 2STB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

In some applications it makes sense to add a test point or a disconnect element to the feed through terminal for testing and safety purposes. With test disconnect terminals you measure electric circuits in the absence of voltage. While the disconnecting points clearance and creepage distance is not assessed in dimensional terms, the specified rated impulse voltage strength must be proven.

**General ordering data**

|            |   |
|------------|---|
| Version    | SAK Series, Test-disconnect terminal, Rated cross-section: 4 mm <sup>2</sup> , Screw connection, beige, Direct mounting |
| Order No.  | <a href="#">0327960000</a>  |
| Type       | DKT 4/35 2STB   |
| GTIN (EAN) | 4008190089344   |
| Qty.       | 25 pc(s).   |

Creation date March 7, 2023 1:30:32 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## DKT 4/35 2STB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 56.5 mm | Depth (inches)  | 2.224 inch |
| Height     | 65 mm   | Height (inches) | 2.559 inch |
| Width      | 6 mm    | Width (inches)  | 0.236 inch |
| Net weight | 16.55 g |                 |            |

## Temperatures

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C         |                                  |        |

## Material data

|                           |       |        |                |
|---------------------------|-------|--------|----------------|
| Material                  | PA 66 | Colour | beige / yellow |
| UL 94 flammability rating | V-2   |        |                |

## System specifications

|                                     |   |                               |     |
|-------------------------------------|---|-------------------------------|-----|
| Version                             | Screw connection, Spacer,<br>With sockets, One end<br>without connector | End cover plate required      | Yes |
| Number of potentials                | 2   | Number of levels              | 2   |
| Number of clamping points per level | 2   | Number of potentials per tier | 1   |
| Levels cross-connected internally   | No  | PE connection                 | No  |
| Rail                                | TS 35   | N-function                    | No  |
| PE function                         | No  | PEN function                  | No  |

## Additional technical data

|                             |         |                     |                 |
|-----------------------------|---------|---------------------|-----------------|
| Explosion-tested version    | No      | Installation advice | Direct mounting |
| Number of similar terminals | 1       | Open sides          | right           |
| Type of mounting            | Snap-on |                     |                 |

## Conductors for clamping (additional connection)

|   |                     |
|---|---------------------|
| Conductor cross-section, flexible plus<br>plastic collar DIN 46228/1, further<br>connection, max. | 2.5 mm <sup>2</sup> |
|---|---------------------|

## DKT 4/35 2STB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

|   |                      |   |                     |
|---|----------------------|---|---------------------|
| Blade size  | 0.6 x 3.5 mm         | Clamping range, max.  | 4 mm <sup>2</sup>   |
| Clamping range, min.  | 0.13 mm <sup>2</sup> | Clamping screw  | M 3                 |
| Connection cross-section, stranded, max.  | 4 mm <sup>2</sup>    | Connection cross-section, stranded, min.  | 1.5 mm <sup>2</sup> |
| Connection direction  | on side              | Gauge to IEC 60947-1  | A3                  |
| Number of connections   | 4                    | Stripping length  | 9 mm                |
| Tightening torque, max.   | 1 Nm                 | Tightening torque, min.   | 0.5 Nm              |
| Torque level with DMS electric screwdriver  | 2                    | Twin wire-end ferrules, max.  | 1.5 mm <sup>2</sup> |
| Twin wire-end ferrules, min.  | 0.5 mm <sup>2</sup>  | Type of connection  | Screw connection    |
| Wire connection cross section AWG, max.   | AWG 12               | Wire connection cross section AWG, min.   | AWG 26              |
| Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>    | Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, solid core, max.   | 4 mm <sup>2</sup>    | Wire connection cross-section, solid core, min.   | 0.5 mm <sup>2</sup> |

## Disconnect terminals

|                  |          |                      |     |
|------------------|----------|----------------------|-----|
| Cross-disconnect | without  | Integral test socket | Yes |
| Slitting         | Pivoting |                      |     |

## General

|   |                 |   |        |
|---|-----------------|---|--------|
| Installation advice                     | Direct mounting | Rail                                    | TS 35  |
| Standards                               | IEC 60947-7-1   | Wire connection cross section AWG, max. | AWG 12 |
| Wire connection cross section AWG, min. | AWG 26          |   |        |

## Rating data

|                                 |                   |  |        |
|---------------------------------|-------------------|--|--------|
| Rated cross-section             | 4 mm <sup>2</sup> | Rated voltage                                | 400 V  |
| Rated current                   | 10 A              | Current at maximum wires                     | 10 A   |
| Standards                       | IEC 60947-7-1     | Volume resistance according to IEC 60947-7-x | 1 mΩ   |
| Rated impulse withstand voltage | 6 kV              | Power loss in accordance with IEC 60947-7-x  | 1.02 W |
| Pollution severity              | 3                 |  |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000902    | ETIM 7.0    | EC000902    |
| ETIM 8.0    | EC000902    | ECLASS 9.0  | 27-14-11-26 |
| ECLASS 9.1  | 27-14-11-26 | ECLASS 10.0 | 27-14-11-26 |
| ECLASS 11.0 | 27-14-11-26 | ECLASS 12.0 | 27-14-11-26 |

## Environmental Product Compliance

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | b2a5d6d9-3805-40c5-ba4a-6934b0392759 |

Creation date March 7, 2023 1:30:32 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## DKT 4/35 2STB

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

Approvals



ROHS

Conform

### Downloads

|   |   |
|---|---|
| Approval/Certificate/Document of Conformity | <a href="#">EAC certificate</a><br><a href="#">UKCA declaration of conformity</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>   |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a>                                   |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>  |