

BS 25 O.IH SAKT1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Fixing screws fix the short current bridge within the application. If the short current bridge is slid between two adjacent terminal blocks into the short circuit position, it can be fixed by means of a fastening screw. This ensures a permanent connection or short circuit.

General ordering data

Version	SAK Series, Set of fixings
Order No.	0334700000
Type	BS 25 O.IH SAKT1
GTIN (EAN)	4008190118839
Qty.	50 pc(s).

Creation date February 23, 2023 11:42:53 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

BS 25 O.IH SAKT1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	28.7 mm	Depth (inches)	1.13 inch
Height	5.5 mm	Height (inches)	0.217 inch
Width	5.5 mm	Width (inches)	0.217 inch
Diameter	5.5 mm	Net weight	1.7 g

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Steel, Brass	Colour	beige
----------	--------------	--------	-------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	when screwed in
---------------------	-----------------	------------------	-----------------

Dimensions

Diameter	5.5 mm
----------	--------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cabfa93a-285a-4cc9-a7cb-2fefa00bc7a4

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	