

CLI R 1-3 GE/SW -**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

| | |
|------------|-----------------------------|
| Version | CableLine, Mounting mandrel |
| Order No. | 0572901740 |
| Type | CLI R 1-3 GE/SW - |
| GTIN (EAN) | 4032248106691 |
| Qty. | 10 Stück |

Erstellungs-Datum May 26, 2023 5:38:19 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

CLI R 1-3 GE/SW -

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 5 mm | Depth (inches) | 0.197 inch |
| Height | 3 mm | Height (inches) | 0.118 inch |
| Width | 4.2 mm | Width (inches) | 0.165 inch |
| Net weight | 2.2 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

General data

| | | | |
|--|---------------|-----------------------------------|----------------------------|
| Colour | yellow | Colour of printing | black |
| Halogen | Yes | Material | PVC, soft, without Cadmium |
| Material colour according to resistance code | 4 | Number per mandrel | 25 |
| Operating temperature range | -30...80 °C | Operating temperature range, max. | 80 °C |
| Operating temperature range, min. | -30 °C | Orientation of print | horizontal |
| Printed characters | Symbols | Printing | - |
| Printing method | hot-embossing | Recommended industries | Process, Machinery |
| Type of printing | Standard | UL 94 flammability rating | V-0 |
| Version | MultiPack | Width | 4.2 mm |

Conductor and cable markers

| | | | |
|-------------------------------|---------------------|----------------------------------|-------------------------|
| Conductor O.D. | 2.5 - 5 mm | Conductor O.D., max. | 5 mm |
| Conductor O.D., min. | 2.5 mm | Conductor cross-section, max. | 4 mm ² |
| Conductor cross-section, min. | 1.5 mm ² | Cross-section for connected wire | 1.5 - 4 mm ² |
| Halogen | Yes | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-06-29 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|-----------------------------|--|
| Engineering Data | WSCAD |
| Product Change Notification | PCN CableLine_DE PCN CableLine_EN |
| Catalogues | Catalogues in PDF-format |