

**SAKG 54/35 II****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**

Are you looking for an interface from electrical engineering to electronics? To be able to feed through to the electronic devices on the panel sometimes a solder connection or a standard pluggable solution is appropriate.

**General ordering data**

Version	SAK Series, Feed-through terminal, Rated cross-section: 240 mm <sup>2</sup> , Screw connection, medium yellow, Direct mounting
Order No.	<a href="#">0638120000</a>
Type	SAKG 54/35 II
GTIN (EAN)	4008190068646
Qty.	5 pc(s).

## SAKG 54/35 II

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	60.5 mm	Depth (inches)	2.382 inch
Height	122 mm	Height (inches)	4.803 inch
Width	54 mm	Width (inches)	2.126 inch
Net weight	587.6 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

## Material data

Material	KrG	Colour	medium yellow
UL 94 flammability rating	V-0, 5VA		

## System specifications

Version	Stud terminal	End cover plate required	Yes
Number of levels	1	Number of clamping points per level	2
Number of potentials per tier	1	Levels cross-connected internally	No
PE connection	No	Rail	TS 35

## Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Number of similar terminals	1	Open sides	Open
Type of mounting	Snap-on		

## CSA rating data

Certificate No. (CSA)	12400-199	Current size C (CSA)	600 A
Voltage size C (CSA)	600 V	Wire cross section max. (CSA)	500 kcmil
Wire cross section min. (CSA)	300 kcmil		

## Conductors for clamping (rated connection)

Clamping range, max.	240 mm <sup>2</sup>	Clamping range, min.	10 mm <sup>2</sup>
Clamping screw	M 16	Connection direction	on side
Number of connections	1	Tightening torque, max.	60 Nm
Tightening torque, min.	25 Nm	Type of connection	Screw connection
Wire connection cross section AWG, max.	kcmil 500	Wire connection cross section AWG, min.	kcmil 300

## General

Installation advice	Direct mounting	Rail	TS 35
Standards	IEC 60947-7-1	Wire connection cross section AWG, max.	kcmil 500
Wire connection cross section AWG, min.	kcmil 300		

## SAKG 54/35 II

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

## Technical data

### Rating data

Rated cross-section	240 mm <sup>2</sup>	Rated voltage	www.weidmueller.com 1,000 V
Rated current	415 A	Current at maximum wires	415 A
Standards	IEC 60947-7-1	Volume resistance according to IEC 60947-7-x	0.08 mΩ
Rated impulse withstand voltage	8 kV	Power loss in accordance with IEC 60947-7-x	13.28 W
Pollution severity	3		

### UL rating data

Certificate No. (UR)	E60693	Conductor size Factory wiring max. (UR)	500 kcmil
Conductor size Factory wiring min. (UR)	300 kcmil	Conductor size Field wiring max. (UR)	500 kcmil
Conductor size Field wiring min. (UR)	300 kcmil	Current size C (UR)	380 A
Voltage size C (UR)	600 V		

### Classifications

ETIM 6.0	EC000897	ETIM 7.0	EC000897
ETIM 8.0	EC000897	ECLASS 9.0	27-14-11-20
ECLASS 9.1	27-14-11-20	ECLASS 10.0	27-14-11-20
ECLASS 11.0	27-14-11-20	ECLASS 12.0	27-14-11-20

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E60693

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a> <a href="#">MARITREG Certificate</a> <a href="#">Declaration of Conformity</a> <a href="#">CE Declaration of Conformity all terminals</a> <a href="#">UKCA declaration of conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>