

SFX 10/23 MC NE GR V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



SlimFix X are halogen-free conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. SlimFix is an acknowledged and approved marker type in traffic engineering. The SF tool allows easy installation even in case of small markers.

- Halogen-free material
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|--------------------|--|
| Version | SlimFix X, Conductor and cable markers, 7 - 40 mm, 23 x 11 mm, grey |
| Order No. | 1000380000 |
| Type | SFX 10/23 MC NE GR V2 |
| GTIN (EAN) | 40322488 162 17 |
| Qty. | 160 pc(s). |
| compatible printer | 2715590000 2438520000 2438510000 |

SFX 10/23 MC NE GR V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 0.8 mm | Depth (inches) | 0.031 inch |
| Height | 23 mm | Height (inches) | 0.906 inch |
| Width | 11 mm | Width (inches) | 0.433 inch |
| Net weight | 0.62 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|---|--|--------------|
| Colour | grey | Halogen | No |
| Material | Polyamide 66 | Material colour according to resistance code | 8 |
| Number of markers per combination | 1 MultiCard = Conductor and cable markers | Operating temperature range | -40...100 °C |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -40 °C |
| Recommended industries | Transportation, Machinery | Size of labelling field | 23 x 5 mm |
| Type of printing | neutral | UL 94 flammability rating | V-2 |
| Version | Installation with cable ties | Width | 11 mm |

Conductor and cable markers

| | | | |
|-------------------------------|--------------------|----------------------------------|--------------------------|
| Conductor O.D. | 7 - 40 mm | Conductor O.D., max. | 40 mm |
| Conductor O.D., min. | 7 mm | Conductor cross-section, max. | 500 mm ² |
| Conductor cross-section, min. | 16 mm ² | Cross-section for connected wire | 16 - 500 mm ² |
| Halogen | No | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|---------------------------------|
| Engineering Data | CAD data – STEP |
| Engineering Data | EPLAN |

Data sheet

SFX 10/23 MC NE GR V2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

