

THM WO T 24.5/62 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 6.1 - 13.7 mm, 24.5 x 62 mm, white
Order No.	1003420000
Type	THM WO T 24.5/62 WS
GTIN (EAN)	4032248699315
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

Creation date May 4, 2023 4:55:51 PM CEST

Catalogue status 28.04.2023 / We reserve the right to make technical changes.

THM WO T 24.5/62 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.05 mm	Depth (inches)	0.002 inch
Height	24.5 mm	Height (inches)	0.965 inch
Width	62 mm	Width (inches)	2.441 inch
Net weight	603 g		

Temperatures

Operating temperature range	-40...107 °C
-----------------------------	--------------

General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	No
Colour	white	Halogen	Yes
Material	Tedlar polyvinyl fluoride film®	Material colour according to resistance code	9
Number of markers per combination	1 Label reel = Conductor and cable markers	Number per roll	2,500
Operating temperature range	-40...107 °C	Operating temperature range, max.	107 °C
Operating temperature range, min.	-40 °C	Size of labelling field	25 x 24.5 mm
Type of printing	neutral	UL 94 flammability rating	V-0
Version	Self-adhesive	Width	62 mm

Conductor and cable markers

Conductor O.D.	6.1 - 13.7 mm	Conductor O.D., max.	13.7 mm
Conductor O.D., min.	6.1 mm	Conductor cross-section, max.	95 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 95 mm ²
Halogen	Yes	Text field height	25 mm
Text field width	24.5 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
Catalogues	Catalogues in PDF-format

Data sheet

THM WO T 24.5/62 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

