

SAIBM-M8-3P-(IF)**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M8 round plug-in connectors are particularly suited to applications where space is limited.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

General ordering data

Version	Field attachable connector, M8, Female socket, straight
Order No.	1010080000
Type	SAIBM-M8-3P-(IF)
GTIN (EAN)	4032248715305
Qty.	1 pc(s).

SAIBM-M8-3P-(IF)

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 29 g

Temperatures

Operating temperature, min. -40 °C Operating temperature, max. 85 °C

Technical data customisable plug-in connectors

Cable diameter	3.5...5.5 mm	Cable diameter, max.	5.5 mm
Cable diameter, min.	3.5 mm	Coding	none, A
Conductor cross-section, max.	0.5 mm ²	Conductor cross-section, min.	0.14 mm ²
Connection cross-section, max.	0.5 mm ²	Connection cross-section, min.	0.14 mm ²
Contact surface	Gold-plated	Housing main material	CuZn
Insulation strength	10 ⁸ Ω	Number of poles	3
Plugging cycles	≥ 100	Pollution severity	3
Protection degree	IP67	Rated current	4 A
Rated voltage	60 V	Rated voltage	60 V
Shield connection	Yes	Temperature range of housing	-40 ... +85 °C
Threaded ring material	Diecast zinc	Type of connection	Screw connection

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ECLASS 9.0	27-44-01-02
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-02
ECLASS 11.0	27-44-01-02	ECLASS 12.0	27-44-01-16

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E307231

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN