

**VGM40-SS 68 KB 18-25****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

**General ordering data**

Version	VG S (standard stainless steel cable gland), Cable glands, straight, M 40, 9 mm, OD min. 18 - OD max. 25 mm, Stainless steel 1.4305 (303)
Order No.	<a href="#">1009890000</a>
Type	VGM40-SS 68 KB 18-25
GTIN (EAN)	4032248714711
Qty.	20 pc(s).

Creation date March 7, 2023 2:22:47 PM CET

## VGM40-SS 68 KB 18-25

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Length	49.6 mm	Length (inches)	1.953 inch
Net weight	143.7 g		

## Temperatures

Operating temperature	-40 °C...100 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	100 °C		

## Certificate numbers cable gland

Approval conditions	DNV	Certificate no. cable gland (GERMLLOYD)	E-14047
---------------------	-----	---	---------

## General information

AF size	41 mm	AF size 1	41 mm
AF size 2	46 mm	Cable glands	metric, M 40
External thread	M 40	Halogen	Yes
Length of thread	9 mm	Material	Stainless steel 1.4305 (303)
O-Ring	NBR	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Outer cable diameter, max.	25 mm
Outer cable diameter, min.	18 mm	Pitch of thread	1.5 mm
Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K	Seal insert	CR
Sealing	NBR	Tightening torque	22 Nm
Torque for cap nut, max.	31 Nm	Torque for cap nut, min.	29 Nm
Torque for connecting adapter, max.	12.5 Nm	Torque for connecting adapter, min.	11.5 Nm

## Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01

## Approvals

Approvals



ROHS Conform

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity - Standard stainless steel cable gland made from 1.405 (303) stainless steel - DoC DE PS2480 210608 001ISS00</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

Creation date March 7, 2023 2:22:47 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

2