

VGM63-SS 68 KB 34-44**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG S (standard stainless steel cable gland), Cable glands, straight, M 63, 14 mm, OD min. 34 - OD max. 44 mm, Stainless steel 1.4305 (303)
Order No.	1009910000
Type	VGM63-SS 68 KB 34-44
GTIN (EAN)	4032248714735
Qty.	5 pc(s).

Creation date March 7, 2023 2:23:06 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

VGM63-SS 68 KB 34-44

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	67 mm	Length (inches)	2.638 inch
Net weight	424.1 g		

Temperatures

Operating temperature	-40 °C... 100 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	100 °C		

Certificate numbers cable gland

Approval conditions	UL, DNV	Certificate no. cable gland (GERMLLOYD)	E-14047
Certificate no. cable gland (UL)	E-199260		

General information

AF size	65 mm	AF size 1	65 mm
AF size 2	70 mm	Cable glands	metric, M 63
External thread	M 63	Halogen	Yes
Length of thread	14 mm	Material	Stainless steel 1.4305 (303)
O-Ring	NBR	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Outer cable diameter, max.	44 mm
Outer cable diameter, min.	34 mm	Pitch of thread	1.5 mm
Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K	Seal insert	CR
Sealing	NBR	Tightening torque	50 Nm
Torque for cap nut, max.	57 Nm	Torque for cap nut, min.	53 Nm
Torque for connecting adapter, max.	26 Nm	Torque for connecting adapter, min.	24 Nm

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity - Standard stainless steel cable gland made from 1.405 (303) stainless steel - DoC DE PS2480 2 10608 001ISS00
Engineering Data	CAD data - STEP
Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

Creation date March 7, 2023 2:23:06 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

2