

VG 16 HQ K68 9-13**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

| | |
|------------|---|
| Version | Heavy-duty connectors, Accessories, Cable glands, Polycarbonate |
| Order No. | 1016070000 |
| Type | VG 16 HQ K68 9-13 |
| GTIN (EAN) | 4032248725526 |
| Qty. | 1 pc(s). |

Creation date March 7, 2023 2:24:56 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

VG 16 HQ K68 9-13

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 13 g

Temperatures

Limit temperature -20 °C ... 100 °C

General information

| | | | |
|-------------------|-------|--------------|---------------|
| AF size | 27 mm | Cable glands | PG 16 |
| External thread | PG 16 | Material | Polycarbonate |
| Protection degree | IP68 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000441 | ETIM 7.0 | EC000441 |
| ETIM 8.0 | EC000441 | ECLASS 9.0 | 27-14-44-32 |
| ECLASS 9.1 | 27-14-44-32 | ECLASS 10.0 | 27-14-44-32 |
| ECLASS 11.0 | 27-14-44-32 | ECLASS 12.0 | 27-14-08-01 |

Approvals

Approvals



ROHS Conform

Downloads

| | |
|-----------------------------|---|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD |
| Product Change Notification | 20210205 Technical change to HQ Cable Glands 20210205 Technische Änderung zu HQ Kabelverschraubung |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN FL FIELDWIRING EN |