

## SCT-C 7.9/680

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Cable ties are characterised by maximum tying force and a long life. Steel cable ties also offer permanent fastening under extreme conditions such as high temperatures or severe chemical effects.

- Fully coated stainless steel cable ties
- Secure ball locking mechanism for a fast and simple installation
- Can be attached manually or using a tool
- These cables ties are recommended for special applications, such as for use with saline spray, extreme temperatures or corrosive surroundings.

### General ordering data

Version	Cable ties, 7.9 x 680 mm, Stainless steel, polyester coated, 11 12 N
Order No.	<a href="#">1015340000</a>
Type	SCT-C 7.9/680
GTIN (EAN)	4032248724314
Qty.	100 Stück

Erstellungs-Datum May 25, 2023 12:16:53 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## SCT-C 7.9/680

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	0.26 mm	Depth (inches)	0.01 inch
Height	680 mm	Height (inches)	26.772 inch
Width	7.9 mm	Width (inches)	0.311 inch
Net weight	12.14 g		

### Temperatures

Operating temperature range	-80...150 °C	Operating temperature, min.	-80 °C
Operating temperature, max.	150 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	165 °C		

### Installation materials

Bundle diameter, max.	200 mm	Bundle diameter, min.	20 mm
Cable diameter, max.	200 mm	For re-opening	No
Halogen	No	Material	Stainless steel, polyester coated
Operating temperature range, max.	150 °C	Operating temperature range, min.	-80 °C
Tensile strength	1,112 N	Tensile strength (Pound-force)	250 lbf
UV-resistant	No		

### Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E524836

### Downloads

Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**SCT-C 7.9/680**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

**Drawing**

