

KLIPPON STB 2.1 MS HT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



Ideally suited for the energy, process and transportation industries, the Klippon[®] STB enclosure series is the perfect complement to our existing Klippon[®] enclosure portfolio. Enclosures in this series are approved according to international standards such as e.g. the Lloyds Register and EN62208.

- Sheet steel 1.0330, powder-coated in RAL 7032
- Comes with a standard seal that is resistant to high temperatures - extended temperature range of -60°C to +120°C
- Approved according to Lloyds Register and Russian Maritime Register
- Flexible options for fastening the internal mounting rail
- IP66 protection
- Secure, permanent function of the seal is ensured by seal compression protection
- Earthing stud in the cover and base of the enclosure
- Laser cut weld seams for increased quality
- Already welded-on mounting feet guarantee optimum enclosure installation

General ordering data

Version	Klippon STB (Small Terminal Box), Empty enclosure, Sheet steel enclosure, Height: 190 mm, Width: 150 mm, Depth: 90 mm, Material: Sheet steel, Powder-coated, Pebble grey
Order No.	1025010000
Type	KLIPPON STB 2.1 MS HT
GTIN (EAN)	4032248745227
Qty.	1 pc(s).

KLIPPON STB 2.1 MS HT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	90 mm	Depth (inches)	3.543 inch
Height	190 mm	Height (inches)	7.48 inch
Width	150 mm	Width (inches)	5.905 inch
Mounting dimension - width	175 mm	Net weight	2,020 g

Temperatures

Operating temperature	-60 °C...120 °C	Operating temperature, min.	-60 °C
Operating temperature, max.	120 °C		

Cable glands, left

M12	15	M16	10
M20	8	M25	3
M32	3	M40	2
M50	1		

Cable glands, right

M12	18	M16	10
M20	10	M25	3
M32	3	M40	2
M50	1		

Cable glands, top/bottom

M12	15	M16	10
M20	8	M25	3
M32	3	M40	2
M50	1		

Certificate numbers enclosure

Approval conditions	LR, EAC	Certificate No. (EAC)	C-DE.AB54.B.00251.19
Certificate No. (LLOYDSREG)	08_20032	Certificate no. Terminal Box (EAC)	C-DE.AД54.B.00251/19 Ind. Terminal Box
Certificate no., empty enclosure (EAC)	C-DE.HB07.B.00089/20	Declaration of Conformity No. (DoC LVD)	DE PS2620 160412 002ISS01

KLIPPON STB 2.1 MS HT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**General information**

Access opening: height	172 mm	Access opening: width	130 mm
Areas of use	Transportation, Marine engineering, Process industry, Packaging industry	Enclosure attachment	Welded-on mounting foot with 8-mm holes
Flange plate	No	Impact resistance	10 J version standard
Integral fixing	TAS 20 rail welded to floor	Lid	Yes
Lid attachment	M5 hexagonal screw with slot and 10mm distance across flats	Material	Sheet steel
Material thickness of cover	1.5 mm	Material thickness of enclosure	1.5 mm
Max. payload	19.95 kg	Number of lid screws	4
Operating temperature, max.	120 °C	Operating temperature, min.	-60 °C
Protection class (UL)	Type 4, Type 4X	Protection degree	IP66
Seal material	Silicone	Standards	DIN 4102-12
Surface finish	Powder-coated		

Housing earth

Cross-section, max.	25 mm ²	Earth, enclosure, cover	Welded-on M6 x 10 stainless-steel earth stud
Earth, enclosure, external	Welded-on M6 x 16 stainless-steel bolts	Earth, enclosure, internal	Welded-on M6 x 16 stainless-steel bolts

vertical assembly

WDU 10 / ZDU 10	1x15	WDU 16 / ZDU 16	1x13
WDU 2,5 / ZDU 2,5 / IDU 2,5	1x30	WDU 4 / ZDU 4	1x25
WDU 6 / ZDU 6	1x20		

Classifications

ETIM 6.0	EC000261	ETIM 7.0	EC000261
ETIM 8.0	EC000261	ECLASS 9.0	27-18-01-01
ECLASS 9.1	27-18-92-90	ECLASS 10.0	27-18-01-01
ECLASS 11.0	27-18-01-01	ECLASS 12.0	27-18-01-01

Important note

Product information	The fire rating up to E90 acc. to DIN 4102-12 depends on concrete configurations / installations (details see "Declaration of Manufacturer" in "Downloads")
---------------------	---

Approvals

Approvals



ROHS

Conform

KLIPPON STB 2.1 MS HT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	C-DE.A154.B.00251.19 Ind. Terminal Box RUC-DE.BE02.B.00173 08_20032 MPA NRW Certificate - fire rated assembled boxes acc. to DIN 4102-12 EU Declaration of Conformity - Klippon STB Empty Enclosures IND - DoC DE PS2620 160412 002ISS02
Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Tender specification	Klippon STB 2.1 MS HT_1025010000_DE Klippon STB 2.1 MS HT_1025010000_EN
User Documentation	Assembly guidelines - empty enclosures
Catalogues	Catalogues in PDF-format
Brochures	MB KLIPPON ENCL.TECN EN FL KLIPPON STB EN FL SHIPBUILDING 2016 EN FL SHIPBUILDING 2016 EN

KLIPPON STB 2.1 MS HT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Dimensioned drawing

