

## DMC 12/27 MC SDR

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

The DMC markers can be used for labelling switching devices or sub-assemblies. The large (12 x 27 mm) marking surface offers sufficient room for information describing the device and its function. Only one tag size for cable cross-sections from 0.5 – 10 mm<sup>2</sup> enables use on both multi-core control cables and single cores.

**For custom printing:** Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labelling specifications.

### General ordering data

Version	DMC, Device markers, 1.5 - 7.5 mm, 12 x 27 mm, To customer specification
Order No.	<a href="#">1038830000</a>
Type	DMC 12/27 MC SDR
GTIN (EAN)	4032248768080
Qty.	10 pc(s).
compatible printer	<a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>

Creation date May 4, 2023 5:02:27 PM CEST

Catalogue status 28.04.2023 / We reserve the right to make technical changes.

## DMC 12/27 MC SDR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	5 mm	Depth (inches)	0.197 inch
Height	12 mm	Height (inches)	0.472 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	1.67 g		

## Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

## General data

Advice label	Colour based on customer requirements (Please send M-Print PRO file)	Colour	To customer specification
Colour of printing	black	Halogen	No
Material	Polyamide 66	Number of markers per combination	1 MultiCard = Device markers
Operating temperature range	-40...100 °C	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Printed characters	Based on customer requirements (Please send M-Print PRO file)
Printing method	MC Laser	Width	27 mm

## Device markers

Halogen	No
---------	----

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>