

## ESG X20 10/7 MC NE RT

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|                     |  |
|---------------------|--|
| Version             | ESG, Device markers x 7 mm, PA 66, Colour: red, pluggable                        |
| Order No.           | <a href="#">1026570000</a>   |
| Type                | ESG X20 10/7 MC NE RT  |
| GTIN (EAN)          | 403224875 1839   |
| Qty.                | 240 pc(s).   |
| compatible printer  | <a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a> |
| Alternative product | <a href="#">1038930000</a>   |

## ESG X20 10/7 MC NE RT

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.8 mm  | Depth (inches)  | 0.031 inch |
| Height     | 10 mm   | Height (inches) | 0.394 inch |
| Width      | 7 mm    | Width (inches)  | 0.276 inch |
| Net weight | 0.438 g |                 |            |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

### General data

|  |                |                                   |                              |
|--|----------------|-----------------------------------|------------------------------|
| Application/manufacture                      | B&R X20 System | Colour                            | red                          |
| Halogen                                      | No             | Material                          | PA 66                        |
| Material colour according to resistance code | 2              | Number of markers per combination | 1 MultiCard = Device markers |
| Operating temperature range                  | -40...100 °C   | Operating temperature range, max. | 100 °C                       |
| Operating temperature range, min.            | -40 °C         | UL 94 flammability rating         | V-2                          |
| Version                                      | pluggable      | Width                             | 7 mm                         |

### Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">CAD data – STEP</a>  |
| Engineering Data            | <a href="#">WSCAD</a>  |
| Product Change Notification | <a href="#">Technical change - DE</a><br><a href="#">Technical change - EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                                       |

**Data sheet**

**ESG X20 10/7 MC NE RT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

