

## ESG 9/10 MC SDR

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Version	ESG, Device markers x 10 mm, PA 66, Colour: To customer specification, pluggable
Order No.	<a href="#">1038880000</a>
Type	ESG 9/10 MC SDR
GTIN (EAN)	4032248768134
Qty.	40 pc(s).
compatible printer	<a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>

## ESG 9/10 MC SDR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.031 inch
Height	9 mm	Height (inches)	0.354 inch
Width	10 mm	Width (inches)	0.394 inch
Net weight	0.45 g		

## Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

## General data

Colour	To customer specification	Colour of printing	black
Halogen	No	Material	PA 66
Number of markers per combination	1 MultiCard = Device markers	Operating temperature range	-40...100 °C
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Printed characters	Based on customer requirements (Please send M-Print PRO file)	Printing method	MC Laser
UL 94 flammability rating	V-2	Version	pluggable
Width	10 mm		

## Device markers

Halogen	No
---------	----

## Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>