

KLIPPON STB 6 SS E

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Similar to illustration



Abbildung ähnlich

Ideally suited for the energy, process and transportation industries, the Klippon® STB enclosure series is the perfect complement to our existing Klippon® enclosure portfolio. Enclosures in this series are approved according to international standards such as e.g. EN62208 and EN60079-0/7 (ATEX).

- Mirror-polished or electropolished stainless steel 1.4404 (316L), 1.5 mm
- High-temperature-resistant seal as standard - extended temperature range of -60°C to +100°C for Ex application (+120°C only for industrial application)
- Approved according to ATEX, IECEx, cULus, Lloyds Register, Germanischer Lloyd, GL DNV and INMETRO
- Flexible options for fastening the internal mounting rail
- IP66 protection
- Secure, permanent function of the seal is ensured by seal compression protection
- Earthing stud in the cover and base of the enclosure
- Laser cut weld seams for increased quality
- Already welded-on mounting feet guarantee optimum enclosure installation

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Version	Klippon STB (Small Terminal Box), Empty enclosure, stainless steel enclosure, Height: 250 mm, Width: 400 mm, Depth: 130 mm, Material: Stainless steel 1.4404 (316L), electropolished, silver
Order No.	1058870000
Type	KLIPPON STB 6 SS E
GTIN (EAN)	4032248800742
Qty.	1 Stück

KLIPPON STB 6 SS E

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	130 mm	Depth (inches)	5.118 inch
Height	250 mm	Height (inches)	9.842 inch
Width	400 mm	Width (inches)	15.748 inch
Mounting dimension - height	150 mm	Mounting dimension - width	425 mm
Net weight	5,481 g		

Temperatures

Operating temperature	-60 °C...100 °C	Operating temperature, min.	-60 °C
Operating temperature, max.	100 °C		

Cable glands, left

M12	64	M16	33
M20	30	M25	16
M32	10	M40	6
M50	4	M63	2

Cable glands, right

M12	36	M16	21
M20	18	M25	10
M32	8	M40	3
M50	2	M63	2

Cable glands, top/bottom

M12	64	M16	33
M20	30	M25	16
M32	10	M40	6
M50	4	M63	2

Certificate numbers enclosure

Approval conditions	ATEX, DNV, EAC, IECEX, INMETRO, LR, RMRS, UL AEx Class Div., UL AEx Class Zone, cULus, KC, CCC	Attestation of Conformity No. (AoC)	DE PS2620 160308 001ISS02
Certificate No. (ATEX)	IBEXU07ATEX1147U	Certificate No. (EAC)	C-DE.HB07.B.00089-20
Certificate No. (IECEX)	IECEXIBE09.0018U	Certificate No. (LLOYDSREG)	08_20032
Certificate no. (INMETRO)	IEX13.0003	Certificate no. (cULus)	E256877
Certificate no. Terminal Box (AEx)	E223792	Certificate no. Terminal Box (ATEX)	IBEXU07ATEX1148
Certificate no. Terminal Box (EAC)	C-DE.HB07.B.00089/20 Ex Terminal Box; C-DE.A154.B.00251/19 Ind. Terminal Box	Certificate no. Terminal Box (IECEX)	IECEX IBE 09.0019
Certificate no. Terminal Box (INMETRO)	LMP 21.0018	Certificate no. Terminal Box (KOSHA)	16-AV4BO-0247X
Certificate no. empty enclosure (ATEX)	IBEXU 07ATEX1147U	Certificate no. empty enclosure (IECEX)	IECEX IBE 09.0018U
Certificate no. empty enclosure (INMETRO)	IEEx 13.0002U	Certificate no., empty enclosure (EAC)	C-DE.HB07.B.00089/20
Declaration of Conformity No. (DoC LVD)	DE PS2620 160412 001ISS01		

KLIPPON STB 6 SS E

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

General information

Access opening: height	230 mm	Access opening: width	882 mm
Areas of use	Explosive risk zone, Packaging industry, Transportation, Process industry, Marine engineering	Enclosure attachment	Welded-on mounting foot with 8-mm holes
Flange plate	No	Impact resistance	10 J version standard, 7 J ATEX version
Integral fixing	TAS 20 rail welded to floor	Lid	Yes
Lid attachment	M5 hexagonal screw with slot and 10mm distance across flats	Material	Stainless steel 1.4404 (316L)
Material thickness of cover	1.5 mm	Material thickness of enclosure	1.5 mm
Number of lid screws	4	Operating temperature, max.	100 °C
Operating temperature, min.	-60 °C	Protection class (UL)	Type 4, Type 4X
Protection degree	IP66	Seal material	Silicone
Surface finish	electropolished	Torque for lid screws	2.5 Nm

Housing earth

Cross-section , max.	25 mm ²	Earth, enclosure, cover	Welded-on M6 x 10 stainless-steel earth stud
Earth, enclosure, external	Welded-on M6 x 16 stainless-steel bolts	Earth, enclosure, internal	Welded-on M6 x 16 stainless-steel bolts

horizontal assembly

WDU 10 / ZDU 10	2x37	WDU 16 / ZDU 16	2x30
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x72	WDU 4 / ZDU 4	2x60
WDU 6 / ZDU 6	2x46		

vertical assembly

WDU 10 / ZDU 10	3x22	WDU 16 / ZDU 16	3x18
WDU 2,5 / ZDU 2,5 / IDU 2,5	3x42	WDU 4 / ZDU 4	3x35
WDU 6 / ZDU 6	3x27		

Classifications

ETIM 6.0	EC002503	ETIM 7.0	EC002503
ETIM 8.0	EC002503	ECLASS 9.0	27-18-05-02
ECLASS 9.1	27-18-05-02	ECLASS 10.0	27-18-05-02
ECLASS 11.0	27-18-05-02	ECLASS 12.0	27-18-05-02

Important note

Product information The ambient temperature for the assembly will be reduced to +60°C and the surface temperature to +100°C.

KLIPPON STB 6 SS E

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

Technische Daten

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E256877

Downloads

Approval/Certificate/Document of Conformity	C-DE.HB07.B.00089-Empty Enclosures and Ex. Terminal Box C-DE.AJ54.B.00251.19 Ind. Terminal Box CCC 2020322303002356 STB Assembly Enclosure UKCA TÜV 22 UKEX 7099 U UKCA TÜV 22 UKEX 7100 Attestation of Conformity - Klippon STB Empty Enclosures - AoC DE PS2620 160308 001ISS04 RUC-DE.BE02.B.00173 08_20032 IBEXU07ATEX1148 IECEXIBE09.0018U IECEXIBE09.0019 IEX13.0002U IEX13.0003 15.40041.250 16-AV4BO-247X 59358-08 IBEXU07ATEX1147U INMETRO Certificado LMP 21.0018 KLIPPON STB EU Declaration of Conformity - Klippon STB Empty Enclosures Ex - DoC DE PS2620 160412 001ISS01
Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
Tender specification	Klippon STB 6 SS E_1058870000_DE Klippon STB 6 SS E_1058870000_EN
User Documentation	Assembly guidelines - empty enclosures
Catalogues	Catalogues in PDF-format
Brochures	MB OVERV. PROCESS WD DE MB KLIPPON ENCL.TECN EN MB PROCESS EN FL KLIPPON STB EN FL SHIPBUILDING 2016 EN FL SHIPBUILDING 2016 EN

KLIPPON STB 6 SS E

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

Dimensioned drawing

