

**IE-C5DD4UG0003MCAMCA-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Assembled IE cables, PROFINET, Cat. 5, PUR, green, drag-chain compatible, M12

**General ordering data**

|            |   |
|------------|---|
| Version    | Dragline cable, PROFINET, M12 D-code – IP 67 angled pin, M12 D-code – IP 67 angled pin, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PUR, 0.3 m |
| Order No.  | <a href="#">1059890003</a>  |
| Type       | IE-C5DD4UG0003MCAMCA-E  |
| GTIN (EAN) | 4032248988389   |
| Qty.       | 1 pc(s).  |

Creation date March 13, 2023 11:18:22 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## IE-C5DD4UG0003MCAMCA-E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |       |                 |             |
|------------|-------|-----------------|-------------|
| Length     | 0.3 m | Length (inches) | 11.811 inch |
| Net weight | 50 g  |                 |             |

## Temperatures

|                             |                |                             |                |
|-----------------------------|----------------|-----------------------------|----------------|
| Storage temperature         | -50 °C...70 °C | Operating temperature       | -40 °C...70 °C |
| Operating temperature, min. | -40 °C         | Operating temperature, max. | 70 °C          |
| Installation temperature    | -20 °C...60 °C |                             |                |

## Cable specific standards

|                               |   |                              |                          |
|-------------------------------|---|------------------------------|--------------------------|
| Standard, insulating material | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3) | Standard, shielding material | DIN EN 13602 Cu-ETP-A..B |
| Standard, wire material       | DIN EN 13602 Cu-ETP-A                             |                              |                          |

## General standards

|                         |         |
|-------------------------|---------|
| Certificate no. (cULus) | E316369 |
|-------------------------|---------|

## Standards

|                               |   |                              |                          |
|-------------------------------|---|------------------------------|--------------------------|
| Standard, insulating material | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3) | Standard, shielding material | DIN EN 13602 Cu-ETP-A..B |
| Standard, wire material       | DIN EN 13602 Cu-ETP-A                             |                              |                          |

## Cable structure

|                              |   |                                       |   |
|------------------------------|---|---------------------------------------|---|
| Arrangement of wire cores    | Star-quad   | Colour sequence or wires - wire pairs | white, yellow, blue, orange                       |
| Complete shielding           | Aluminium foil, Shielding braid made from copper wiring | Cross-section                         | 4*AWG 22/7 - 0.32 mm <sup>2</sup>                 |
| Diameter of inner sheathing  | 3.9 mm  | Filler                                | As central element                                |
| Insulation                   | PE  | Insulation cross-section              | 1.5 mm  |
| Material sheath              | PUR   | Number of wires                       | 4   |
| Overlap of shielding braid   | 85 %  | Sheath diameter, max.                 | 6.7 mm  |
| Sheath diameter, min.        | 6.3 mm  | Shielding colour                      | green (RAL 6018)                                  |
| Sheathing material thickness | 0.9 mm  | Shielding                             | SF/UTP  |
| Shielding braid thickness    | 0.13 mm   | Standard designations                 | 2YH(ST)C11Y<br>2x2x0,75/1,5-100 LI VZN<br>GN FRNC |
| Strands                      | 7   | Wire core insulation thickness        | 0.38 mm   |
| Wire material                | Stranded tin-plated copper wire                         |                                       |   |

## Electrical properties of cable

|                               |   |
|-------------------------------|---|
| Capacity at 1 kHz             | 52 nF/km                                    |
| Category                      | Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B) |
| Characteristic impedance      | 100 ± 15 Ω at 1–100 MHz                     |
| Deviation                     | 40 ns/100m                                  |
| Loop resistance               | 120 Ω/km                                    |
| Operating voltage (UL rating) | Operating voltage 600 V                     |
| Operating voltage (UL rating) | 600 V undefined                             |
| Operating voltage, UL         | 600 V                                       |

Creation date March 13, 2023 11:18:22 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

**IE-C5DD4UG0003MCAMCA-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data**

|                                |                                      |
|--------------------------------|--------------------------------------|
| Resistance differential        | 3 %                                  |
| Signal propagation time        | 5.3 ns/m                             |
| Speed                          | 180 m/min                            |
| Test voltage: wire-wire-shield | 2000 V <sub>eff</sub> , 50 Hz, 1 min |
| Transfer impedance             | 20 mΩ/m at 10 MHz                    |

**Mechanical and material properties of cable**

|                                 |  |                                |                                |
|---------------------------------|--|--------------------------------|--------------------------------|
| Abrasion resistance             | very good                              | Acceleration                   | 4 m/s <sup>2</sup>             |
| Bending cycles                  | 3 Mio                                  | Fire propagation               | No                             |
| Halogen                         | halogen-free, according to IEC 60754-2 | Min. bending radius, once only | 5 x cable diameter             |
| Min. bending radius, repetitive | 7.5 x cable diameter                   | Pulling force                  | ≤ 150 N                        |
| Resistance to oils              | in accordance with IEC 60811-2-1       | Resistance to spread of flame  | in accordance with IEC 60332-1 |
| Silicone-free                   | Yes                                    | Speed                          | 180 m/min                      |
| UV-resistant                    | Yes                                    |                                |                                |

**Plug**

|           |   |            |   |
|-----------|---|------------|---|
| Plug left | M12, D, IP67, male contact, angled 90°, plug, Plastic, shielded | Plug right | M12, D, IP67, male contact, angled 90°, plug, Plastic, shielded |
|-----------|---|------------|---|

**Plug, left**

|                |                               |
|----------------|-------------------------------|
| Connector left | M12 D-code – IP 67 angled pin |
|----------------|-------------------------------|

**Plug, right**

|                 |                               |
|-----------------|-------------------------------|
| Connector right | M12 D-code – IP 67 angled pin |
|-----------------|-------------------------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002599    | ETIM 7.0    | EC002599    |
| ETIM 8.0    | EC002599    | ECLASS 9.0  | 27-06-03-08 |
| ECLASS 9.1  | 27-06-03-08 | ECLASS 10.0 | 27-06-03-08 |
| ECLASS 11.0 | 27-06-03-08 | ECLASS 12.0 | 27-06-03-08 |

**Environmental Product Compliance**

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | 67cf1078-beca-4687-860b-dc475a6ec24a |

**Approvals**

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate no. (cULus) | E316369    |

Creation date March 13, 2023 11:18:22 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

3

**IE-C5DD4UG0003MCAMCA-E**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">CAD data – STEP</a>   |
| User Documentation | <a href="#">MAN IE GUIDE DE</a><br><a href="#">MAN IE GUIDE EN</a>          |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>                                    |
| Brochures          | <a href="#">FL FIELDWIRING EN</a><br><a href="#">PI PROFINET CABLING EN</a> |

---

**Data sheet**

**IE-C5DD4UG0003MCAMCA-E**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

---

|     |        |     |
|-----|--------|-----|
| M12 |        | M12 |
| 1   | yellow | 1   |
| 2   | white  | 2   |
| 3   | orange | 3   |
| 4   | blue   | 4   |

---

---

---