

TS 35X15/LL 2M/ST/ZN/O

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Version	Rail, TS 35, TS 35 x 15, with slot, Steel, galvanic zinc plated and passivated
Order No.	1071680000
Type	TS 35X15/LL 2M/ST/ZN/O
GTIN (EAN)	4032248884636
Qty.	2 m

Creation date February 28, 2023 5:00:18 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

TS 35X15/LL 2M/ST/ZN/O
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data
Dimensions and weights

Depth	15 mm	Depth (inches)	0.591 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	590 g		

Mounting rail

Installation advice	Direct mounting		
Length of the terminal rail	nominal	2,000 mm	
	min.	0 mm	
	max.	2,000 mm	
Material	Steel		
Pre-punched mounting rail	Yes		
Short circuit strength corresponds to E-Cu wire	50 mm ²		
Short-time withstand current according to IEC 60947-7-2	6 kA/1s		
Slit gap	11 mm		
Slit gap			
Slit length	25 mm		
Slit length			
Slit width	5.2 mm		
Slit width			
Standards	In accordance with DIN EN 60715		
Surface finish	galvanic zinc plated and passivated		

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format



TS 35X15/LL 2M/ST/ZN/O

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Product image



Similar to illustration