

IE-C5DS4VG0060MCSMCS-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables, PROFINET, Cat. 5, PVC, green, M12

General ordering data

Version	System cable, M12 D-code – IP 67 straight pin, M12 D-code – IP 67 straight pin, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 6 m
Order No.	1102190060
Type	IE-C5DS4VG0060MCSMCS-E
GTIN (EAN)	4050118517620
Qty.	1 pc(s).

Creation date March 13, 2023 11:59:21 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

IE-C5DS4VG0060MCSMCS-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	6 m	Length (inches)	236.22 inch
Net weight	431 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...70 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	70 °C
Installation temperature	-40 °C...80 °C		

Cable specific standards

Standard, assembly	UL-Style 21694	Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)
Standard, shielding material	DIN EN 13602 Cu-ETP-A..B	Standard, wire material	DIN EN 13602 Cu-ETP-A

Standards

Standard, assembly	UL-Style 21694	Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)
Standard, shielding material	DIN EN 13602 Cu-ETP-A..B	Standard, wire material	DIN EN 13602 Cu-ETP-A

Cable structure

Arrangement of wire cores	Star-quad	Colour sequence or wires - wire pairs	white, yellow, blue, orange
Complete shielding	Aluminium foil, Shielding braid made from copper wiring	Cross-section	4*AWG 22/7 - 0.32 mm ²
Diameter of inner sheathing	4.05 mm	Filler	As central element
Insulation	PE	Insulation cross-section	1.5 mm
Material sheath	PVC	Number of wires	4
Overlap of shielding braid	85 %	Sheath diameter, max.	6.7 mm
Sheath diameter, min.	6.3 mm	Sheathing colour	green (RAL 6018)
Sheathing material thickness	0.9 mm	Shielding	SF/UTP
Shielding braid thickness	0.13 mm	Standard designations	2YY(ST)CY 2x2x0,75/1,5-100 LI VZN GN
Strands	7	Wire material	Stranded tin-plated copper wire

Electrical properties of cable

Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)		
Characteristic impedance	100 ± 5 Ω at 100MHz		
Loop resistance	120 Ω/km		
Operating voltage (UL rating)	Operating voltage	600 V	
Operating voltage (UL rating)	600 V undefined		
Operating voltage, UL	600 V		
Signal propagation time	5.3 ns/m		
Test voltage: wire-wire-shield	2000 V _{eff} , 50 Hz, 1 min		
Transfer impedance	20 mΩ/m at 10 MHz		

Creation date March 13, 2023 11:59:21 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

2

IE-C5DS4VG0060MCSMCS-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Mechanical and material properties of cable**

Abrasion resistance	good	Halogen	Yes
Min. bending radius, once only	3.5 *diameter	Min. bending radius, repetitive	7.5 x cable diameter
Resistance to spread of flame	in accordance with IEC 60332-1 / UL 1685		

Plug

Plug left	M12, D, IP67, male contact, straight, plug, Plastic, shielded	Plug right	M12, D, IP67, male contact, straight, plug, Plastic, shielded
-----------	---	------------	---

Plug, left

Connector left	M12 D-code – IP 67 straight pin
----------------	---------------------------------

Plug, right

Connector right	M12 D-code – IP 67 straight pin
-----------------	---------------------------------

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08	ECLASS 12.0	27-06-03-08

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

Data sheet**IE-C5DS4VG0060MCSMCS-E****Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Drawings****Wiring**

M12		M12
1	yellow	1
2	white	2
3	orange	3
4	blue	4