

IE-KSF-PKV14M-KLROB-1.5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	
Order No.	1103660015
Type	IE-KSF-PKV 14M-KLROB-1.5M
GTIN (EAN)	4032248922512
Qty.	1 Stück

Erstellungs-Datum May 24, 2023 1:33:59 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

IE-KSF-PKV14M-KLROB-1.5M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 293.6 g

Temperatures

Operating temperature -40 °C...70 °C Operating temperature, min. -40 °C
 Operating temperature, max. 70 °C

Electrical properties

Operating voltage 30 V

General standards

Connector standard IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14

Standards

Connector standard IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14

Cable structure

Sheath diameter, max. 9.3 mm Sheathing colour black (similar to RAL 9005)

Electrical properties of cable

Operating voltage 30 V

Mechanical and material properties of cable

Min. bending radius, once only 5 x cable diameter Min. bending radius, repetitive 10 x cable diameter

Classifications

ETIM 6.0	EC001579	ETIM 7.0	EC001579
ETIM 8.0	EC001579	ECLASS 9.0	27-06-24-90
ECLASS 9.1	27-06-24-00	ECLASS 10.0	27-06-05-01
ECLASS 11.0	27-06-05-01	ECLASS 12.0	27-06-05-01

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Approvals

ROHS Conform

IE-KSF-PKV14M-KLROB-1.5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads


User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN

IE-KSF-PKV14M-KLROB-1.5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen



STECKANLEITUNG
TYPE 1000

PA	BEZUG	BEZUGSWERT
1	PAIR 1 (B)	
2	PAIR 1 (B)	
3		
4	PAIR 2 (B)	
5	PAIR 2 (B)	
6		
7	PAIR 3 (B)	
8	PAIR 3 (B)	
9		
10		