

THM WO 50.8/150 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 8.1 - 39.7 mm, 50.8 x 150 mm, yellow
Order No.	1109180000
Type	THM WO 50.8/150 GE
GTIN (EAN)	4032248885329
Qty.	1 pc(s).

Creation date May 4, 2023 5:16:38 PM CEST

Catalogue status 28.04.2023 / We reserve the right to make technical changes.

THM WO 50.8/150 GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	50.8 mm	Height (inches)	2 inch
Width	150 mm	Width (inches)	5.905 inch
Net weight	610 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Polyacrylate adhesive	Colour	yellow
Halogen	No	Material	Polyester film
Material colour according to resistance code	4	Number of markers per combination	1 Label reel = Conductor and cable markers
Number per roll	500	Operating temperature range	-40...150 °C
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Size of labelling field	25.4 x 50.8 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	150 mm		

Conductor and cable markers

Conductor O.D.	8.1 - 39.7 mm	Conductor O.D., max.	39.7 mm
Conductor O.D., min.	8.1 mm	Conductor cross-section, max.	500 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 500 mm ²
Halogen	No	Text field height	25.4 mm
Text field width	50.8 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
Catalogues	Catalogues in PDF-format

Data sheet

THM WO 50.8/150 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

