

**HDC HP 250 M 95****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Version	HDC insert, Pin, 3000 V, 250 A, Crimp connection, Size: 250
Order No.	<a href="#">1119100000</a>
Type	HDC HP 250 M 95
GTIN (EAN)	4032248900350
Qty.	1 pc(s).

Creation date March 7, 2023 4:18:36 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## HDC HP 250 M 95

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Length	82.6 mm	Length (inches)	3.252 inch
Diameter	32 mm	Net weight	131.03 g

## Temperatures

Limit temperature	-50 °C ... 120 °C
-------------------	-------------------

## General data

BG	250	Conductor cross-section	95 mm <sup>2</sup>
Free from halogens	false	Insulating material	Polyamide with fibre optic
Insulation strength	10 <sup>10</sup> Ω	Material	Copper alloy
Pollution severity	PD 2 (PD 3)	Rated current (DIN EN 61984)	250 A
Rated impulse voltage (DIN EN 61984)	15 kV	Rated voltage (DIN EN 61984)	3,000 V
Series	HighPower	Size	250
Surface finish	Silver passivated	Type	Pin
UL 94 flammability rating	V-0	Volume resistance	≤0.1 mΩ

## Connection data PE

Connection type PE	Crimp connection, Screw connection
--------------------	------------------------------------

## Power contact

Rated current (DIN EN 61984), power contact	250 A	Rated impulse voltage (DIN EN 61984), power contact	15 kV
Rated voltage (DIN EN 61984), power contact	3,000 V	Stripping length, performance contact	24 mm
Type of connection, power contact	Crimp connection		

## Version

BG	250	Conductor cross-section, max.	95 mm <sup>2</sup>
Conductor cross-section, min.	95 mm <sup>2</sup>	Material	Copper alloy
Size	250	Stripping length, rated connection	24 mm
Surface finish	Silver passivated	Type of connection	Crimp connection
Volume resistance	≤0.1 mΩ	Wire connection cross section AWG, max.	AWG 3/0

## Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ECLASS 9.0	27-44-02-04
ECLASS 9.1	27-44-02-04	ECLASS 10.0	27-44-02-04
ECLASS 11.0	27-44-02-04	ECLASS 12.0	27-44-02-04

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

## HDC HP 250 M 95

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

Approvals



ROHS

Conform

### Downloads

Approval/Certificate/Document of  
Conformity

[Manufacturer's declaration](#)

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)  
[FL FIELDWIRING EN](#)

**HDC HP 250 M 95**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Drawings**

