

SAIBW-M-4/7 M12 ZF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

Tension-clamp connection delivers excellent functional security and reduced installation times. With this technology the conductor is plugged into the tension clamp without a wire-end ferrule (optionally with wire-end ferrule). The connection between the conductor and tension clamp is vibration-resistant and boasts long-term stability.

General ordering data

Version	Field attachable connector, M12, Socket, angled
Order No.	1125550000
Type	SAIBW-M-4/7 M12 ZF
GTIN (EAN)	4032248907861
Qty.	1 pc(s).

SAIBW-M-4/7 M12 ZF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 70 g

Technical data customisable plug-in connectors

Cable diameter	4...6 mm (PG7)	Cable diameter, max.	6 mm
Cable diameter, min.	4 mm	Coding	A
Conductor cross-section, max.	0.5 mm ²	Conductor cross-section, min.	0.25 mm ²
Connection cross-section, max.	0.5 mm ²	Connection cross-section, min.	0.14 mm ²
Contact surface	Gold-plated	Housing main material	PA
Insulation strength	10 ⁸ Ω	Number of poles	4
Plugging cycles	≥ 100	Pollution severity	3
Protection degree	IP67	Rated current	4 A
Rated voltage	250 V	Rated voltage	250 V (4-pole) / 60 V (5-pole)
Shield connection	Yes	Temperature range of housing	-40 ... +85 °C
Threaded ring material	Diecast zinc	Type of connection	Tension-clamp connection

General Info

Number of poles	4	Connection 1	M12
Connection 2	Tension-clamp	Housing main material	PA
Connection thread	M12	Contact surface	Gold-plated
Protection degree	IP67	Plugging cycles	≥ 100

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ECLASS 9.0	27-44-01-02
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-02
ECLASS 11.0	27-44-01-02	ECLASS 12.0	27-44-01-16

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Imidazolidine-2-thione 96-45-7
SCIP	bcee35cf-c0f5-43d2-8daf-65ab0d08641a

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	CAD data – STEP
User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN

Creation date March 7, 2023 4:23:35 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

2