

THM ET S7 300-2 TU**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM ET S7 non-adhesive, roll-packaged labels are used to label the SIMATIC ET 200S and S7-modules from Siemens.

The M-Print® PRO software can be used to individually print the THM ET S7 labels with a THM printer. Labels can be easily separated. The THM MultiMark printer ensures highly-resistant printing.

General ordering data

| | |
|--------------------|--|
| Version | THM, Device markers, 103.8 x 17.3 mm, Siemens, Turquoise |
| Order No. | 1161730000 |
| Type | THM ET S7 300-2 TU |
| GTIN (EAN) | 4032248950782 |
| Qty. | 1 pc(s). |
| compatible printer | 2599430000 2599440000 |

Creation date May 4, 2023 5:22:50 PM CEST

Catalogue status 28.04.2023 / We reserve the right to make technical changes.

THM ET S7 300-2 TU

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 0.08 mm | Depth (inches) | 0.003 inch |
| Height | 103.8 mm | Height (inches) | 4.087 inch |
| Width | 17.3 mm | Width (inches) | 0.681 inch |
| Net weight | 700 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -50...100 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|------------------|-----------------------------------|-------------------------------|
| Application/manufacturer | Siemens | Approval acc. to UL 969 | No |
| Colour | Turquoise | Halogen | No |
| Material | Polypropylene | Number of markers per combination | 1 Label reel = Device markers |
| Number per roll | 1,000 | Operating temperature range | -50...100 °C |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -50 °C |
| Printing method | Thermal transfer | UL 94 flammability rating | HB |
| Version | halogen-free | Width | 17.3 mm |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ECLASS 9.0 | 27-40-06-29 |
| ECLASS 9.1 | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | WSCAD |
| Catalogues | Catalogues in PDF-format |

Data sheet

THM ET S7 300-2 TU

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

